



DO NOT SCALE METRIC THIRD ANGLE PROJECTION

ITEM NR.	DESCRIPTION OF ACCESSORY	1	2	3	4	5	6	7	8	9
5	BUSHING WITH THROUGH HOLE 3,1 DIA.									
5	BUSHING WITH THREAD 4-40 UNC									
5	BUSHING WITH THREAD M3									
4	FEMALE SCREWLOCK WITH THREAD 4-40 UNC									
4	FEMALE SCREWLOCK WITH THREAD M3									
6	BOARDLOCK									

HOW TO ORDER:  
 25 POS. -----> Z-338311-Y  
 PREFIX FOR ACCESSORIES }  
 BASIC PARTNR. }  
 SUFFIX FOR PLATING }

PLATING SUFFIX "Y"  
 GOLD OVER NICKEL AS PER PERFORMANCE LEVEL 2 (DIN 41652)  
 SOLDERPART : 2,5µm BRIGHT SnPb. } -Y = -2

- ① GROOVE INDICATES VERSION WITH 4-40 UNC INNER THREAD; WITHOUT GROOVE INDICATES VERSION WITH M3 INNER THREAD.
- ② CAVITY IDENTIFICATION AT FRONT SIDE ONLY.
- ③ PARTNUMBER AND DATE CODE.
- 4 WHEN BOARDLOCKS ARE USED, CONNECTOR CAN BE USED FOR PCB THICKNESS OF 1,6 mm ONLY.
- 5 SHELL HAS 2x8 GROUNDING SPRINGS; PITCH IS 3,6 mm

- ITEM NRS./MATERIAL :
- ① SHELL = BRIGHT TINPLATED STEEL
  - ② HOUSING = GLASSFILLED POLYESTER, COLOR : BLACK
  - ③ CONTACTS = PHOSPHORBRONZE (PLATING : SEE TABLE ABOVE)
  - ④ FEMALE SCREWLOCK = TINPLATED STEEL (INNER THREAD 4-40 UNC OR M3)
  - ⑤ BUSHING = TINPLATED STEEL (INNER THREAD 4-40 UNC OR M3 OR 3,1 DIA. THROUGH HOLE)
  - ⑥ BOARDLOCK = TINPLATED PHOSPHORBRONZE
  - ⑦ STAND-OFF = ULTRAMID COLOR : BLACK

-				CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED			
-				© COPYRIGHT 19 - BY AMP-HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING. THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION			
D	EH-1417-99	P.W.	W.C.	19-02-00	AMP-HOLLAND B.V. 's-Hertogenbosch, The Netherlands.		
C	EH-0033-99	D.K.	W.S.	29 JAN 99	AMP		
B	EH-1385-98	W.S.	W.S.	04-09-98	HDP-20 SIZE 3 VERTICAL+ PLUG HEADER; WITH SOLDER CONTACTS		
A	EH-0029-98	JvL	C.S.	15-01-98	NAME		
0	EH-0694-97	JvL	C.S.	03-07-97	DWG.No. C-338311		
LTR.	REVISION RECORD	DR.	CHK.	DATE	REV.LTR.	SHEET	1 of 1
DR.:	J.v.LIEMPT	CHK.:	C.SOUISA	APP.:	E.ELEUTENS	DWG.No.	C-338311
DATE:	03-07-97	DATE:	03-07-97	DATE:	-	REV.LTR.	D
	11		10		9		8
							7
							6
							5
							4
							3
							2
							1