

RETAINER PLATE
MATERIAL: ALUMINUM
FINIH: CHROMATE CONVERSION

CAPTIVE SCREWS
MATERIAL: STAINLESS STEEL
FINISH: PASSIVATED
QTY 2

31.30
MAX

M22 X 1.0

32.50
MAX

4 POSITION MT FIBER INSERT
MATERIAL: NICKEL SILVER COPPER
INSERT RETAINING RING
MATERIAL: STAINLESS STEEL
FINISH: PASSIVATED
INTERFACIAL SEAL
MATERIAL: RUBBER
COLOR: RED

FIBER OPTIC MT FERRULE CABLE ASSEMBLY
SHOWN FOR REFERENCE ONLY
FIBER OPTIC CABLE ASSEMBLIES
CAN BE ORDERED SEPARATELY

SHELL BODY
MATERIAL: ALUMINUM
FINISH: CHROMATE CONVERSION

- 1 FINISH: OLIVER DRAB, CADMIUM.
2 FINISH: NICKEL, ELECTROLESS
3 FINISH: NICKEL PTFE

45 DEGREE
INSERT OPTION

5.80 MAX
PANEL THICKNESS

24.61

24.61

Ø 23.01 MIN. (FRONT ENTRY)
Ø 26.59 MIN. (REAR ENTRY)

Ø 3.25
4X

MASTER KEYWAY

KEYING ORIENTATION	A	B	C	D
N	95°	141°	208°	236°
A	113°	156°	182°	292°
B	90°	145°	195°	252°

RECOMMENDED PANEL CUT-OUT

KEYING ORIENTATION DETAIL

1-2358897-8	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY B, NICKEL PTFE, 45° INSERT	3
1-2358897-7	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY B, NICKEL PTFE	3
1-2358897-6	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY A, NICKEL PTFE, 45° INSERT	3
1-2358897-5	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY A, NICKEL PTFE	3
1-2358897-4	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY N, NICKEL PTFE, 45° INSERT	3
1-2358897-3	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY N, NICKEL PTFE	3
1-2358897-2	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY B, NICKEL, 45° INSERT	2
1-2358897-1	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY B, NICKEL	2
1-2358897-0	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY B, OLIVE DRAB, 45° INSERT	1
2358897-9	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY B, OLIVE DRAB	1
2358897-8	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY A, NICKEL, 45° INSERT	2
2358897-7	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY A, NICKEL	2
2358897-6	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY A, OLIVE DRAB, 45° INSERT	1
2358897-5	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY A, OLIVE DRAB	1
2358897-4	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY N, NICKEL, 45° INSERT	2
2358897-3	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY N, NICKEL	2
2358897-2	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY N, OLIVE DRAB, 45° INSERT	1
2358897-1	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY N, OLIVE DRAB	1

ASSEMBLY PART NUMBER	DESCRIPTION
----------------------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. FABIAN	16JUL2019	TE Connectivity	
DIMENSIONS:		CHK -	-	NAME	
mm		APVD -		PRODUCT SPEC	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		SIZE	
0 PLC ±		WEIGHT		CAGE CODE DRAWING NO	
1 PLC ±		-		RESTRICTED TO	
2 PLC ±0.13		-		A	
3 PLC ±0.013		-		00779	
4 PLC ±		-		C=2358897	
ANGLES		-		SHEET 1 OF 1	
FINISH		-		REV A	
1 2		CUSTOMER DRAWING		SCALE 2:1	