

*new*

# R O V E R P O I N T



EXTENDING  
REEL ADVANTAGES  
EVEN FURTHER

**MEM**


# R O V E R P O I N T

Roverpoint - perhaps the most famous name ever in extension reels - is now better than ever.




## Features and Benefits

- Modern two-tone design
- All three socket outlets can be used at once
- Safety cut-out (on most models) prevents overloading
- Compact design, smooth re-winding and easy storage in cupboards or toolboxes



- All instructions and ratings are clearly indicated
- Slots to aid ventilation
- Bright yellow high visibility cable is attached to a non-rewireable plug with factory made connectors




- The fuse can be changed without dismantling the plug
- Sealed construction prevents tampering and dangerous repairs
- Roverpoint comes in sturdy packaging with detailed instructions for use
- Useable loads are marked on the reel itself - so that vital safety information is always to hand

British designed and made by MEM Ltd., part of a group with over 100 years' experience in producing the very best, the Roverpoint range has the choice, the styling, all the features and benefits for you that give it maximum 'reel-appeal'.

Roverpoint is the name to look out for. With its new modern looks and its wealth of sought-after features, it's all set to become an essential part of everyone's toolbox.

Make sure you put Roverpoint on your shopping list. It's the one you can trust to give you a range of quality products with winning advantages.



NE  
GET  
BEST  
THIS PO  
NEW I  
OF SU  
BRITISH  
EXTEN  
RE

**new**

**R ○ V E R P ⊕ I N T**

## **& REEL CHOICE REEL VALUE**

The Roverpoint range is designed to cover every requirement and every option. It includes a choice of 5, 6, 9, 12 and 18 metre cable lengths, plus the option of 6 amp or 13 amp power ratings.

<b>3960</b>	6 amp extension reel with 5 metres of cable and two socket outlets.
<b>3961</b>	6 amp extension reel with 6 metres of cable and three socket outlets. Includes safety cut-out.
<b>3962</b>	6 amp extension reel with 12 metres of cable and three socket outlets. Includes safety cut-out.
<b>3963</b>	6 amp extension reel with 18 metres of cable and three socket outlets. Includes safety cut-out.
<b>3980</b>	13 amp extension reel with 9 metres of cable and three socket outlets.

All Roverpoint extension reels are British made within quality systems independently assessed by ASTA to BS 5750: Part 2 (ISO 9002). They meet all relevant British and draft international standards including draft cable reel standards.

**MEM**

250v CIRCUIT PROTECTION & CONTROL

**MEM LIMITED**

WHITEGATE  
BROADWAY  
CHADDERTON  
OLDHAM OL9 9QG  
ENGLAND  
TELEPHONE 061 652 1111  
FAX 061-626 1709

**DELTA**

# EXTENSION REEEL

WITH  
THE  
FROM  
POWERFUL  
ANGLE  
SUPERIOR  
1 MADE  
VISION  
IS

**MEM**  
2M (39ft approx)  
6A

SAFETY CUT-OUT  
PRESS TO RESET  
PLUG FUSE SIZE 13A MAX  
DO NOT USE IN WET CONDITIONS

MODEL No F392

IMPORTANT  
GENERATE FIRE HAZARD  
IF IN CONTACT WITH  
WATER

