


383 - 3770

# Honeywell

---



*Representative photograph, actual product appearance may vary.*

## SSCEB31A1B

**Miniature Enclosed Switches Series SSCE: Side Rotary; 11  
1NO SPDT Snap Action; 3 m Cable**

*Due to regional agency approval requirements, some products may not be available in your area. Please contact your regional Honeywell office regarding your product of choice.*

### Features

- Fully sealed - capable of working when submerged
- Compact construction
- Rugged zinc die-cast housing
- Pre-wired or connector versions
- Variable length PUR cable
- Side and bottom exit cable/connector
- Simple two-screw mounting
- Gang mounting capability
- Wide selection of actuators
- IP66/67, IP68 sealing

### Description

The Super sealed CE Series Miniature limit switch has been designed for reliability in the harshest of environments. Its robust design, corrosion limiting features, flexible PUR cable and super sealing allows it to operate fully submerged in a range of fluids. Its small size allows operation in confined spaces. A range of different actuators offers flexibility in application.

# Honeywell

## SSCEB31A1B

Miniature Enclosed Switches Series SSCE: Side Rotary; 1NC 1NO SPDT Snap Action; 3 Cable

Product Specifications	
Availability	Europe; Asia-Pacific
Product Type	Miniature Enclosed Switches
Actuator	Side Rotary
Lever Style	Roller - Standard
Circuitry	1NC 1NO SPDT Snap Action
Ampere Rating	5 A (Thermal)
Supply Voltage	240 Vac
Housing Material	Zinc Die-Cast
Termination Type	3 m Cable
Series Name	SSCE Series
Sealing	IP68, NEMA 1, 3, 6, 6P, 13
Approvals	UL recognized, CSA Certified, CE Certified
CSA File #	LR15775
UL File #	E41859
Mechanical Life	up to 10 million
Operating Temperature Range	-40 °C to 90 °C (-40 °F to 194 °F)
Comment	Bottom Exit Cable
Agency Approvals and Standards	IEC947-5-1, EN60947-5-1
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and controls and relays
Sealed	Industrial

# Honeywell

---

## SSCEB31A1B

Miniature Enclosed Switches Series SSCE: Side Rotary; 1NC 1NO SPDT Snap Action; 3 Cable

### **WARNING**

#### **PERSONAL INJURY**

DO NOT USE these products as safety or emergency stop devices, or in any other application where failure of the product could result in personal injury.

**Failure to comply with these instructions could result in death or serious injury.**

### **WARNING**

#### **MISUSE OF DOCUMENTATION**

- The information presented in this product sheet (or catalog) is for reference only. DO NOT USE this document as product installation information.
- Complete installation, operation and maintenance information is provided in the instructions supplied with each product.

**Failure to comply with these instructions could result in death or serious injury.**

© Copyright Honeywell Inc. 1998-2001 All rights reserved.