

Licence-free PMR 446 Service

With the introduction of the PMR 446 service, there is no longer a need for any form of operating licence.

This new standard is freely available for business, domestic and pleasure use.

Equip today and take advantage of this low-cost instant communications system.

General Specifications

Channel Capacity	8 (fixed for PMR446 service)
Frequency Range	446.00625 to 446.09375
Channel Spacing	12.5 KHz
Modulation Type	F3E
Operating Temperature	-20°C to +70°C
Approval Specification	RF: ETS 300 296, EMC ETS 300 279
Power Supply	3AAA alkaline cells or Ni-MH battery pack
Battery Life (@ 5-5-90 cycle)	alkaline/NIMH 14hr/9hr
Dimensions	80(h) mm x 50(w) mm x 22(d) mm
Weight (with battery)	120 g (4.23 oz)
Battery Voltage - alkaline/Ni-MH	4.5V/3.6V

Your Local Dealer

ENTEL UK Ltd,
3rd Floor, Ridgehill House,
12 Elstree Way, Borehamwood,
Hertfordshire WD6 1JL
Tel +44 (0)20 8236 0032
Fax +44 (0)20 8236 0082
Email sales@entel.co.uk

EURO-WAVE is a trademark of
Entel UK Ltd

EURO-WAVE™ PMR 446 TRANSCIVER

- ▶ No licence required
- ▶ No line rental
- ▶ No call charges
- ▶ Up to 3km range
- ▶ Ultra compact
- ▶ Ultra-clear audio

Actual size, choice of 3 colours



Weighing just 124 grams,
innovative EURO-WAVE
features large LCD display
with menu-driven options.
Ease of operation assured.

Entel UK

EURO-WAVE™

PMR 446 TRANSCIVER

An essential communications tool for action sports, special events, the construction industry, security, warehouse stock control and family safety.

EURO-WAVE provides clear, cost-free local communications (up to 3km) on construction sites, indoor and outdoor events, sporting and leisure activities, and keeps adults in touch with children at play.

Supplied complete with non-removable antenna, user guide, rear clip (non-removable) and carry strap.



Tough rubberised case available in three colours:

servicable black

high-visibility yellow

distinctive blue

A professional tool for connecting people

ACCESSORISE...

THE CASE COLLECTION


The EURO-WAVE is supported by a wide range of useful accessories. Protect your transceiver from weather and damage with these attractive purpose-designed cases.



1 AQ1 Waterproof aqua bag & strap



2 CLC1N Protective nylon case and shoulder strap



3 CLC1T Protective transparent case



4 CLC1L Protective leatherette case



5 CSA1 Dual slot 1.5hr rapid & trickle charger

See the full range of accessories at www.entele.co.uk

POWER SUPPLY
EURO-WAVE will operate on 3 AAA batteries (not supplied). Charging options include: Dual-slot rapid & trickle charger for 230v, 110v or 12v operation (vehicle use).



6 CNB1 Spare 3.6 v 550mAh Ni-MH battery pack

7 CMP1 Compact lightweight remote speaker microphone



8 CHP1 Single earpiece lightweight headset with boom microphone. As above with VOX option - CHP1V

9 EAP1 Covert style earpiece and microphone with in-line PTT switch. As above without mic - EAP1

MICROPHONES AND HEADSETS
Remote or hands-free use is facilitated by the range of microphones and headsets supplied for your EURO-WAVE.

