

# Control and signalling units Ø 22

Harmony style 4

Pushbuttons, switches and pilot lights, with chromium plated metal bezel

Characteristics :  
pages 1/10 to 1/13  
References :  
pages 1/14 to 1/53  
Dimensions :  
pages 1/54 to 1/61


General

1


## Description

The Ø 22, style 4 range of control and signalling units comprises :

### Complete units XB4-B




Pushbuttons




Pilot lights

### Sub-assemblies for user assembly ZB4-B




Pushbuttons:  
Head and body sub-assemblies



Pilot lights :  
Head and body sub-assemblies

### Component parts and accessories ZB



# Control and signalling units Ø 22

Harmony style 4

Pushbuttons, switches and pilot lights, with chromium plated metal bezel

Characteristics :  
pages 1/10 to 1/13  
References :  
pages 1/14 to 1/53  
Dimensions :  
pages 1/54 to 1/61

General (continued)

## Schematic library

### Pushbuttons and Emergency stop pushbuttons

Pushbutton N/O contact	Pushbutton N/C contact	Mushroom head, spring return N/O contact	Emergency stop latching mushroom head. Push-pull N/C contact
Emergency stop trigger action mushroom head Push-pull N/O + N/C contact	Emergency stop trigger action mushroom head Turn to release - N/C contact	Emergency stop trigger action mushroom head Key release - N/C contact	Emergency stop trigger action mushroom head Turn to release N/O + N/C contact
Emergency stop trigger action mushroom head Key release N/O + N/C contact	Double headed pushbutton N/O + N/C contact		

### Selector switches

Selector switch - 2 position, stay put N/O contact	Selector switch - 3 position, stay put N/O + N/O contact	Selector switch - 3 position, 2 spring return to centre N/O + N/O contact	Selector switch - 2 position, stay put, key withdrawal LH position - N/O contact
Selector switch - 2 position, spring return from right to left, key withdrawal LH position N/O contact			

### Pilot lights

Pilot light with BA 9s incandescent bulb	LED pilot light	Pilot light with integral transformer, 110/120 V ~ primary, 6 V secondary BA 9s incandescent bulb

### Illuminated pushbuttons and selector switches

Illuminated pushbutton BA 9s incandescent bulb N/O + N/C contact	Illuminated pushbutton LED N/O + N/C contact	Illuminated pushbutton with integral transformer, 110/120 ~ 50/60 Hz primary, 6 V secondary. BA 9s incandescent bulb N/O + N/C contact	Double-headed pushbutton with LED pilot light N/O + N/C contact
Illuminated selector switch LED - 2 position stay put N/O + N/C contact			

### Joystick controllers

2 direction Without spring return	2 direction With spring return	4 direction Without spring return	4 direction With spring return

# Control and signalling units Ø 22

Harmony style 4

Pushbuttons, switches and pilot lights, with chromium plated metal bezel

Complete units, XB4-B

General


Characteristics :  
pages 1/10 to 1/13  
References :  
pages 1/14 to 1/53  
Dimensions :  
pages 1/54 to 1/61

1

Complete units  
ready for mounting

Contact functions



Pushbuttons,  
spring return



Flush push  
XB4-BA●1/BA42  
see page 1/14

XB4-BA3311  
see page 1/14

XB4-BA4322  
see page 1/14





Booted flush push  
XB4-BP●1/BP42  
see page 1/14

Projecting push  
XB4-BL42  
see page 1/14

Mushroom head  
XB4-BC21  
see page 1/14




Double-headed pushbuttons,  
spring return



Flush push + projecting push  
XB4-BL845  
see page 1/14

Booted  
flush push + projecting push  
XB4-BL945  
see page 1/14

Ø 40 Emergency stop and  
mushroom head pushbuttons  
without/with trigger action






Push-pull  
XB4-BT42/BT845  
see page 1/15

Turn to release  
XB4-BS542/BS8445  
see page 1/15

Key release  
XB4-BS142/BS9445  
see page 1/15

Selector switches  
and key switches



Standard black handle  
XB4-BD  
see page 1/15

Long black handle  
XB4-BJ  
see page 1/15

Key switches  
XB4-BG  
see page 1/15

# Control and signalling units Ø 22

Harmony style 4

Pushbuttons, switches and pilot lights, with chromium plated metal bezel

Complete units, XB4-B


Characteristics :  
pages 1/10 to 1/13  
References :  
pages 1/14 to 1/53  
Dimensions :  
pages 1/54 to 1/61

General (continued)

## Complete units ready for mounting


### Pilot lights

## Signalling functions




With integral LED

[XB4-BVB/BVG/BVM](#)  
see page 1/16



For BA 9s bulb  
Direct supply

[XB4-BV6](#)  
see page 1/17




Via integral transformer

[XB4-BV3/BV4](#)  
see page 1/17


## Combined contact and signalling functions

### Illuminated pushbuttons, spring return, flush push




With integral LED

[XB4-BW3•B5/BW3•G5/BW3•M5](#)  
see page 1/18



For BA 9s bulb  
Direct supply


[XB4-BW3•65](#)  
see page 1/18



Via integral transformer

[XB4-BW3•35/BW3•45](#)  
see page 1/19


### Double-headed pushbuttons, spring return, with pilot light



With integral LED

[XB4-BW84•5](#)  
see page 1/19

### Illuminated selector switches, standard handle



With integral LED

[XB4-BK12•B5/BK12•G5/BK12•M5](#)  
see page 1/19

# Control and signalling units Ø 22

Harmony style 4

Pushbuttons, switches and pilot lights, with chromium plated metal bezel

Sub-assemblies, ZB4-B

General


Characteristics :  
pages 1/10 to 1/13  
References :  
pages 1/14 to 1/53  
Dimensions :  
pages 1/54 to 1/61

1


## Non illuminated units for user assembly

Pushbuttons, spring return, without marking

### Body sub-assemblies



Screw clamp terminals  
ZB4-BZ10●/BZ141  
see page 1/20



Plug-in connector  
ZB4-BZ10●4/BZ1414  
see page 1/20

Pushbuttons, spring return, with marking

“Push-push to release” pushbuttons


Double-headed pushbuttons, spring return

## Contact functions

### Head sub-assemblies



Flush push without cap  
ZB4-BA0  
see page 1/21



Flush push with set of 6 colour caps  
ZB4-BA9  
see page 1/21



Flush push  
ZB4-BA●  
see page 1/21



Flush push for insertion of legend  
ZB4-BA●8  
see page 1/21



Projecting push  
ZB4-BL●  
see page 1/21



Recessed push  
ZB4-BA●6  
see page 1/21



Booted flush push  
ZB4-BP●  
see page 1/21



Booted flush push for insertion of legend  
ZB4-BP●8  
see page 1/21



Flush push  
ZB4-BA●3●/●4●  
ZB4-BA334/335  
see page 1/22



Projecting push  
ZB4-BL●3●  
see page 1/22




Flush push  
ZB4-BH0●  
see page 1/22



Projecting push  
ZB4-BH●  
see page 1/22




Flush pushes (IP 40/IP 66)  
Without/with markings  
ZB4-BA81  
ZB4-BA82  
see page 1/23



ZB4-BA91  
ZB4-BA92  
see page 1/23



Flush push + projecting push (IP 40/IP 66)  
Without/with markings  
ZB4-BL83  
ZB4-BL84  
see page 1/23



ZB4-BL93  
ZB4-BL94  
see page 1/23

# Control and signalling units Ø 22

Harmony style 4

Pushbuttons, switches and pilot lights, with chromium plated metal bezel

Sub-assemblies, ZB4-B


Characteristics :  
pages 1/10 à 1/13  
References :  
pages 1/14 à 1/53  
Dimensions :  
pages 1/54 à 1/61

General (continued)

## Non illuminated units for user assembly (continued)


Mushroom head pushbuttons, spring return

### Body sub-assemblies



Screw clamp terminals  
ZB4-BZ10●/BZ141  
see page 1/20

Mushroom head pushbuttons, latching with or without trigger action




Plug-in connector  
ZB4-BZ10●4/BZ1414  
see page 1/20

Selector switches and key switches

Toggle switches


## Contact functions

### Head sub-assemblies




○ ●  
● ●  
● ●  
● ●  
Ø 30  
Ø 40  
Ø 60

Spring return  
ZB4-BC/BR  
see page 1/24




● ●  
● ●  
Ø 40  
Ø 60

Push-pull  
ZB4-BT84 ZB4-BT●/BX●  
see page 1/25



● ●  
● ●  
● ●  
Ø 30  
Ø 40  
Ø 60

Turn to release  
ZB4-BS8●4 ZB4-BS4●/BS5●/BS6●  
see page 1/25



● ●  
● ●  
Ø 30  
Ø 40  
Ø 60


Key release  
ZB4-BS9●4/BS7●/BS1●/BS2●  
see page 1/25




Std. black handle (1)  
ZB4-BD  
see page 1/26




Long blk. handle (1)  
ZB4-BJ  
see page 1/26



Knurled blk. knob (1)  
ZB4-BD●9  
see page 1/26



Key switches (2)  
ZB4-BG  
see page 1/27




2 positions  
ZB4-BD●8  
see page 1/52

(1) Switch handle and knob positions



(2) Key withdrawal positions for key switches  
⌘ Key withdrawal positions



# Control and signalling units Ø 22

Harmony style 4

Pushbuttons, switches and pilot lights, with chromium plated metal bezel

Sub-assemblies, ZB4-B

General (continued)


Characteristics :  
pages 1/10 to 1/13  
References :  
pages 1/14 to 1/53  
Dimensions :  
pages 1/54 to 1/61

1


Pilot lights  
for user assembly

## Signalling units

### Body sub-assemblies Integral LED



Screw clamp terminals  
ZB4-BVB/BVG/BVM  
see page 1/28




Plug-in connector  
ZB4-BVB•4/BVG•4/BVM•4  
see page 1/28

### Head sub-assemblies



With lens mounted  
ZB4-BV0•3  
see page 1/29




With 5 separate lenses not mounted  
ZB4-BV003  
see page 1/29

### Body sub-assemblies for BA 9s bulb



Direct supply  
Screw clamp terminals  
ZB4-BV6  
see page 1/29



Via integral transformer  
Screw clamp terminals  
ZB4-BV•/BV3D•/BV5D•  
see page 1/29

### Head sub-assemblies



With lens mounted  
ZB4-BV0•  
see page 1/29

# Control and signalling units Ø 22

## Harmony style 4

Pushbuttons, switches and pilot lights, with chromium plated metal bezel  
Sub-assemblies, ZB4-B


Characteristics :  
pages 1/10 to 1/13  
References :  
pages 1/14 to 1/53  
Dimensions :  
pages 1/54 to 1/61

General (continued)


### Illuminated pushbuttons and selector switches for user assembly

Illuminated pushbuttons, spring return

#### Body sub-assemblies Integral LED



Screw clamp terminals  
ZB4-BW0B/BW0G/  
BW0M  
see pages 1/30 et 3




Plug-in connector  
ZB4-BW0B●●4/  
BW0G●●4/BW0M●●4  
see pages 1/32 et 5


Double headed pushbuttons, spring return, with pilot light

Illuminated "push-push to release" pushbuttons and illuminated selector switches with standard handle

#### Body sub-assemblies For BA 9s bulb



Direct supply  
Screw clamp terminals  
ZB4-BW06  
see page 1/34



Via integral transformer  
Screw clamp terminals  
ZB4-BW03/4/5/3D/5D  
see page 1/34

### Combined contact and signalling functions

#### Head sub-assemblies



Flush push

ZB4-BW3●●3  
see page 1/35

Flush push with illuminated ring

ZB4-BW9●●3  
see page 1/35

Flush push for insertion of legend

ZB4-BA●●8  
see page 1/35




Booted flush push

ZB4-BW5●●3  
see page 1/35



Projecting push

ZB4-BW1●●3  
see page 1/35




Flush pushes  
Without/with markings

ZB4-BW81●●●3,  
see page 1/36




ZB4-BW82●●●3  
see page 1/36



Flush push + projecting push  
Without/with markings

ZB4-BW83●●●3,  
see page 1/36



ZB4-BW84●●●3  
see page 1/36




Flush or projecting  
"push-push to release"

ZB4-BH0●●3/BH●●3  
see page 1/36



Selector switches with  
standard handle

ZB4-BK1●●3  
see page 1/37



Illuminated pushbuttons, spring return

#### Head sub-assemblies



Flush push

ZB4-BW3  
see page 1/35



Projecting push

ZB4-BW1  
see page 1/35