

**S. BRANNAN & SONS LIMITED**  
**COMPANY STANDING INSTRUCTIONS**

S. Brannan & Sons Limited,  
 Leconfield Estate,  
 CLEATOR MOOR,  
 Cumbria CA25 5QE.  
 Tel;- 01946/816600  
 Fax;- 01946/816625

CSI NO:- 501/3  
 REV:- 1 PAGE 1 OF 1  
 DATE:- DECEMBER 2003  
 AUTHORISED .....  
INTERNAL DISTRIBUTION;-  
 Personnel  
 Sales

**SAFETY DATA SHEET FOR MERCURY FREE MAX-MIN THERMOMETER**

The liquid in glass thermometers produced by S. Brannan & Sons Limited, contain expansion media comprising substances and preparations which produce no risk to health, safety or environment when encased in the glass bulb and capillary.

If the instrument is broken during use, minimal risk is presented because of the small volume of materials being used. The following information is supplied as an aid to further reduce risk.

As the Company may change constituent materials, users should check that they are in possession of the most recent revision of this Safety Data Sheet.

1. **MEDIUM CONSTITUENTS**

<b>CHARACTERISTIC</b>	<b>TL 2000 AQUEOUS SOLUTION INORGANIC SALT</b>	<b>PETROLEUM FRACTION</b>	<b>BEROL</b>
FLAMMABILITY	N/A	F.P. (+2C)	F.P.(>100C)
SELECTED SAFETY PHRASES	(S24) AVOID CONTACT WITH SKIN	(S24) AVOID CONTACT WITH SKIN (S62) IF SWALLOWED DO NOT INDUCE VOMITING, SEEK MEDICAL ADVICE	(S26) IN CASE OF CONTACT WITH EYES, RINSE IMMEDIATELY WITH PLENTY OF WATER, SEEK MEDICAL ADVICE
SELECTED RISK PHRASES	(R22) HARMFUL IF SWALLOWED	(R11) HIGHLY FLAMMABLE (R65) MAY CAUSE LUNG DAMAGE IF SWALLOWED	(R41) RISK OF SERIOUS DAMAGE TO EYE
MAXIMUM VOLUME PER INSTRUMENT	0.1ml	1.1ml	0.00001ml
DYE CHARACTERISATION	EUROCERT GREEN S (EC NO. E142)		

2. **FIRST AID DATA**

If any of the media is ingested seek medical attention. Skin/eye contact - wash with water, and seek medical attention.

3. **SPILLAGE**

Disposal, consistent with local authority regulations.