



Wave+Plus Magnifiers

Wave+Plus Magnifiers - the industry's first rectangular lensed illuminated magnifiers. These magnifiers feature a 3.5-diopter (1.88X) lens with a 13" focal length and a 6.75" x 4.5" distortion-free viewing area. Two 13-watt compact fluorescent lamps with individual lamp switching. Blue indicator lights are located on either side of the magnifier head. UL/CUL listed. Standard, ESD-Safe or UV models available.



- 6.75" x 4.5" precision-ground white crown optical-quality glass lens
- Adjustable neck for positioning the magnifier head at the proper viewing angle so as to ensure the operator maintains correct posture
- Lighting: two 13-watt quad compact fluorescent tubes
- Dual switches for independent lighting controls
- Magnification: 3.5 diopter lens (1.88X)
- Total magnification possible 4.35X
- Blue indicator lights for each lamp (indicating on/off fluorescent tube)
- Heavy duty K-arm. 5" square steel tubing - 20 gauge CRS
- ABS plastic construction with polycarbonate lamp (bulb) covers
- 5 year warranty

ESD-Safe Magnifiers are designed for use in static-

RELATED PRODUCTS



AH-Edge Mount Bracket



C-Surface Mount



WAVE+Plus 5D

Wave+Plus Magnifiers

CODES

WAVE+PLUS MAGNIFIERS

Article Number	Light Source	Watt	Weight	Arm Length	Mount	Ctn.	Diopter	Colors
17845BK	Quad Compact Fluorescent	2x13W	8.8	45.0/1143	Edge mount	1	3.5	■
17845LG	Quad Compact Fluorescent	2x13W	8.8	45.0/1143	Edge mount	1	3.5	■
17846BK	Quad Compact Fluorescent	2x13W	8.8	30.0/762	Edge mount	1	3.5	■
17846LG	Quad Compact Fluorescent	2x13W	8.8	30.0/762	Edge mount	1	3.5	■
17847BK	Quad Compact Fluorescent	2x13W	35.3	30.0/762	Base mount	2	3.5	■
17847LG	Quad Compact Fluorescent	2x13W	35.3	30.0/762	Base mount	2	3.5	■

WAVE+PLUS MAGNIFIERS - ESD-SAFE

Article Number	Light Source	Watt	Weight	Arm Length	Mount	Ctn.	Diopter	Colors
17900BK	Quad Compact Fluorescent	2x13W	8.8	45.0/1143	Edge mount	1	3.5	■
17902BK	Quad Compact Fluorescent	2x13W	8.8	30.0/762	Edge mount	1	3.5	■
17904BK	Quad Compact Fluorescent	2x13W	35.3	30.0/762	Base mount	2	3.5	■

WAVE+PLUS MAGNIFIERS - UV

Article Number	Light Source	Watt	Weight	Arm Length	Mount	Ctn.	Diopter	Colors
17915BK	Quad Compact Fluorescent	2x13W	8.8	45.0/1143	Edge mount	1	3.5	■

LENS DATA

Code	Diopter primary	Total Magnification (x)	Total Magnification (%)	Focal Length (mm)
17845BK	3.50	1.9	188	285.7
17845LG	3.50	1.9	188	285.7
17846BK	3.50	1.9	188	285.7

