



**EATON**

**MEM**

**Eaton's Moulded Accessory Range (EMA)**  
Product Focus

**Stylish, wiring  
accessories for  
modern applications**





- Independently approved to latest BS & IEC standards
- Robust high quality thermoplastic covers
- Crack resistant for arduous conditions
- Screw caps to conceal fixing screws
- Aesthetically appealing front plate design enables side by side mounting
- Colour matched with existing ranges



## Eaton's Moulded Accessory Range (EMA)

Quality and value from Eaton - the global solutions selling provider



Eaton's Moulded Accessory Range (EMA) of white moulded wiring accessories has been independently approved to the latest British Standards and IEC Standards.

Designed with colour matching and aesthetics in mind, the range boasts an appealing front plate design. This enables easy side by side mounting of switches and sockets.


Manufactured in a robust high quality thermoplastic, the range offers a comprehensive selection of solutions that combine reliability and durability with quick and simple installation.

Eaton's EMA products take the lead in providing easy installation features which include:

- Screw caps to conceal fixing screws to give a clean finish
- Clear terminal markings
- Printed legends available on request

Eaton's MEM white moulded wiring accessories are the perfect choice for a wide range of residential and commercial projects where quality is essential.

## Switches



<b>E011</b>	10A 1G 1W
<b>E012</b>	10A 2G 1W
<b>E013</b>	10A 3G 1W
<b>E021</b>	10A 1G 2W
<b>E022</b>	10A 2G 2W
<b>E023</b>	10A 3G 2W
<b>E024</b>	10A 4G 2W

<b>E015</b>	10A 1G bellpush
<b>E015PR</b>	10A 1G switch push marked 'PRESS'
<b>E017</b>	10A intermediate
<b>E048</b>	10A 3 pole fan isolator
<b>E401</b>	16A hotel card switch


**Standards**  
To BSEN 60669-1

**Dimensions**  
1G – 86mm x 86mm  
2G – 86mm x 146mm

**Standards**  
To BSEN 60669-1

**Dimensions**  
1G – 86mm x 86mm  
2G – 86mm x 146mm





### Connection Units




<b>E200</b>	13A unswitched connection unit
<b>E200N</b>	13A unswitched + neon
<b>E201</b>	13A fused switched
<b>E201N</b>	13A fused switched + neon
<b>E210</b>	20A flex outlet plate
<b>E212</b>	Cable outlet adaptor plate for fused connection unit and 20A switch

**Standards**  
 To BS1363: Part 4  
 20A flex outlet plate: To BS5733

**Dimensions**  
 1G – 86mm x 86mm

### Sockets



<b>E111</b>	13A 1G unswitched socket
<b>E511</b>	13A 1G switched socket
<b>E511N</b>	13A 1G switched socket + neon
<b>E512</b>	13A 2G switched socket
<b>E512N</b>	13A 2G switched socket + neon
<b>E521</b>	13A 1G DP switched socket 2 E terms
<b>E522</b>	13A 2G DP SW socket 2 E terms
<b>E315</b>	15A 1G switched socket
<b>E370</b>	Shaver socket dual voltage 240V/110AC
<b>E461</b>	16A universal 2 pin socket

**Standards**  
 13A sockets: To BS1363: Part 2  
 15A sockets: To BS546  
 Shaver socket: To BS3535: Part1

**Dimensions**  
 1G – 86mm x 86mm  
 2G – 86mm x 146mm

### 20A Switches



<b>E301</b>	20A DP switch
<b>E301N</b>	20A DP switch with neon
<b>E303</b>	20A DP switch marked 'water heater'
<b>E303N</b>	20A DP switch with neon marked 'water heater'
<b>E304N</b>	20A DP switch with neon marked 'air conditioner'

**Standards**  
 20A switches: To BSEN 60669-1

**Dimensions**  
 1G – 86mm x 86mm




### 45A Switches

### Communication Outlets

### Rotary Dimmers

### Push on / Push off Action Dimmers



- E322** 45A DP switch

---

- E322N** 45A DP switch with neon

---

- E325** 45A DP cooker control unit

---

- E325N** 45A DP cooker control unit with neon

---

- E326N** 45A DP switch with neon marked 'cooker'

---

- E345** 45A cable outlet with terminals

---

- E351** 1G TV co-axial outlet

---

- E351D** 1G TV co-axial outlet dual clamp

---

- E355** 1G SAT outlet

---

- E356** 2G TV SAT outlet

---

- E360** 1G telephone outlet master

---

- E361** 1G telephone outlet secondary

---

- E362** 1G telephone outlet RJ11

---

- E363** 1G RJ45 outlet CAT 6

---

- E9511** 1000W 1G 1W rotary tungsten NON EUROPEAN

---

- E9551** 500W 1G 1W rotary tungsten NON EUROPEAN

---

- E9552** 500W 2G 1W rotary tungsten NON EUROPEAN

---

- E9751** 500W 1G 1W fan controller NON EUROPEAN

---

- E9131** 250W 1G 2W dimmer push

---

- E9132** 250W 2G 2W dimmer push

---

- E9141** 400W 1G 2W dimmer push

---

**Standards**  
 45A switch: To BSEN 60669-1  
 45A cooker control: To BS4177

**Standards**  
 TV Outlets: To BS6312: 2.2  
 TV Co-axial: To BS3041-2

These Dimmers are produced for non-European countries.

**Standards**  
 To BS5518: 1977 and BSEN 55014-1:1977

**Dimensions**  
 1G – 86mm x 86mm  
 2G – 86mm x 146mm

**Dimensions**  
 1G – 86mm x 86mm

**Dimensions**  
 1G – 86mm x 86mm

**Dimensions**  
 1G – 86mm x 86mm



### Grid Coverplates



**E801**



**E802**



**E803**



**E804**

**E801** 1G grid coverplate

**E802** 2G grid coverplate

**E803** 3G grid coverplate

**E804** 4G grid coverplate

Suitable for use with Eaton's MEM Spectra grid range. See Spectra range product guide.


**Dimensions**

1-2G – 86mm x 86mm  
3-4G – 86mm x 146mm

### Voice/Data Module Frame



**E872**



**E874**

**E872** 2 module data plate

**E874** 4 module data plate

Suitable for use with Eaton's MEM 50mm x 25mm module range. See Spectra range product guide.

**Dimensions**

1G – 2G – 86mm x 86mm  
3G – 4G – 86mm x 146mm

### Blank Plates



**E391**



**E392**

**E391** 1G blank plate

**E392** 2G blank plate

**Dimensions**

1G – 86mm x 86mm  
2G – 86mm x 146mm

# Stylish, modern Wiring Accessories



It's never been easier to choose and install aesthetically pleasing contemporary wiring accessories that look good with any decor.



Eaton's electrical business is a global leader in electrical control, power distribution, uninterruptible power supply and industrial automation products and services. Eaton's global electrical brands, including Cutler-Hammer®, Powerware®, Holec® and MEM®, provide customer-driven PowerChain™ Management solutions to serve the power system needs of the industrial, institutional, government, utility, commercial, residential, IT, mission critical and OEM markets worldwide.

Eaton Corporation is a diversified industrial manufacturer with 2006 sales of \$12.4 billion. Eaton is a global leader in electrical systems and components for power quality, distribution and control; fluid power systems and services for industrial, mobile and aircraft equipment; intelligent truck drivetrain systems for safety and fuel economy; and automotive engine air management systems, powertrain solutions and specialty controls for performance, fuel economy and safety. Eaton has 61,000 employees and sells products to customers in more than 125 countries. For more information, visit [www.eaton.com](http://www.eaton.com).

**Eaton Electric Limited**

P.O. Box 19651  
Riyadh 11445  
Saudi Arabia  
  
tel: +966-1-460-2275  
fax: +966-1-460-2291

**Eaton Electric Limited**

P.O. Box 1270  
Jeddah 21431  
Saudi Arabia  
  
tel: +966-2-6822-750  
fax: +966-2-6622-835

**Eaton Electric Limited**

P.O. Box 1993  
Doha  
Qatar  
  
tel: +974-4654792  
fax: +974-4654792

**Eaton Electric Limited**

P.O. Box 425, 9 Shehab Street  
No. 11 Mohandessin  
Cairo, Egypt  
  
tel: +20-2-338-6170  
fax: +20-2-338-2025

**Eaton Electric Limited**

P.O. Box 510449  
Al Ashrafiyeh  
Amman 11151, Jordan  
  
tel: +962-6-4740-660  
fax: +962-6-4744-660

**Eaton Electric Limited**

P.O. Box 620  
Al Khobar 31952  
Saudi Arabia  
  
tel: +966-3-882-5424  
fax: +966-3-882-5732

**Eaton Electric Limited**

Reddings Lane  
Birmingham B11 3EZ  
United Kingdom  
  
Customer Support Centre  
UK tel: +44(0) 8700 545 333  
UK fax: +44(0) 8700 540 333  
International tel: +44 (0)121 685 2100  
International fax: +44 (0)121 685 2028  
email: [ukcommorders@eaton.com](mailto:ukcommorders@eaton.com)

**Eaton Electric Limited**

Dubai World Trade Center  
Level 23, P.O. Box 9398  
Dubai, United Arab Emirates  
  
tel: +9714-331-3938  
fax: +9714-332-9239  
email:  
[SalesOffDubaiUAE@eaton.com](mailto:SalesOffDubaiUAE@eaton.com)

**Eaton Electric Limited**

P.O. Box 48010  
1st Floor, Liason House  
State House Road  
Nairobi, Kenya  
  
tel: +254 20 2719230  
fax: +254 20 2711969

**Eaton Electric & Engineering Services Limited**

Unit 2206, 22/F Millennium City 1  
Tower 1, 388 Kwun Tong Road  
Kwun Tong, Kowloon  
Hong Kong  
  
tel: +852 31058766  
fax: +852 26152289

