

## EVERBUILD 703 AQUA MULTI PLUS FIX & GROUT TILE ADHESIVE



Colour	Product Code	Pack Size	Box Qty
White	FIX005	500ML	12
	FIX01	1LTR	12
	FIX02	2.5LTR	4
	FIX05	5LTR	1
	FIX10	10LTR	1

### Product Description

EVERBUILD FIX AND GROUT TILE ADHESIVE is a ready mixed brilliant white water resistant wall tile adhesive which is also suitable for grouting.

### Benefits

- Excellent water resistance.
- Extremely high bond strength - over double the B.S. minimum requirement in wet shear (7 days drying, 7 days water immersion followed by shearing whilst wet).
- Compressible - allows for slight thermal movement.
- Dries brilliant white.
- Contains a fungicide - prevents mould growth.
- Ready mixed formula - no mixing, no mess. Apply straight from the tub.
- Easier to apply than most competitive adhesives.
- Extended open time.

### Areas for Use

- Kitchen/Bathroom walls.
- Shower areas.
- Communal and power showers
- Work tops subject to water contact.

### Limitations

- Unsuitable for floors.
- Do not use for swimming pools. Use EVERBUILD FLOOR SET TILE MORTAR
- Do not use externally. Use EVERBUILD FLOOR SET TILE MORTAR OR RAPID SET.
- When used as a grout, allow to dry for 7 days before using showers/baths.

### Surface Preparation

#### PLASTER

New plaster must be a minimum of 4 weeks old before tiling. Tile onto finishing coat only. Prime with EVERBUILD PVA diluted 1:3 with water.

#### PLASTERBOARD/PLYWOOD/CHIPBOARD

Must be braced with seasoned timber at 300mm vertically and horizontally. Use moisture resistant grades. All surfaces and edges must be sealed with EVERBUILD SBR diluted 1:4 with water.

SAND/CEMENT RENDER

Allow at least four weeks drying before tiling. Use a mix design of 3 to 4 parts sand to 1 part cement. Prime with EVERBUILD PVA.

BRICKWORK/BLOCKWORK/CONCRETE BLOCK

Allow at least 4 weeks drying time before rendering or plastering. Do not fix directly to blockwork.

EXISTING GLAZED TILES/FORMICA

Roughen surfaces with abrasive sander and prime with EVERBUILD PVA diluted 1:1 with water. Apply adhesive whilst still tacky. Allow at least 5 days before grouting.

PAINTED SURFACES

Not recommended for direct application to emulsion or limewash paints. Remove loose material and prime with EVERBUILD PVA Mix diluted 1:4 with water.

For gloss paints, degrease and score with knife to provide key for adhesive. Allow at least five days drying before grouting.

**Application**

**AS AN ADHESIVE**

All surfaces should be clean, dry and free of dust and loose material before commencing. Refer to directions for specific surfaces.

Surfaces to be tiled must be clean, dry and sound. Porous surfaces, including plaster, must be primed with Everbuild PVA Bond diluted 1 to 3 with water and allowed to dry before tiling. Allow new plaster to dry at least one month before tiling. Apply adhesive to wall at a depth of 3-6mm (no less than 3mm, no greater than 6mm) combing out an area of no greater than 1m<sup>2</sup> at a time. In dry situations, use a suitable notched trowel across the surface of the adhesive before placing the tiles into position and securing with a slight twist action to remove air voids.

In areas subject to wet conditions, do not use a notched trowel. Bed the tiles directly into the surface of the adhesive and again, secure with a slight twist action. In both situations, it is good practice to periodically remove a tile and check that at least 75% of the tile is covered in adhesive. If this is not the case, apply fresh adhesive and reposition.

All surplus adhesive must be removed whilst adhesive is still wet using a dampened cloth or sponge, particularly along grout lines.

**AS A GROUT**

Apply by squeegee or sponge, working well into joints. Ensure no voids remain. Suitable for joint widths up to 6mm. *Allow adhesive to dry for 24 hours before grouting. Allow grout to dry for 7 days before using shower areas/baths.*

**Specific Data**

<b>Appearance</b>	Thick white paste (dries & stays brilliant white)
<b>SG at 20°C</b>	1.7gcm <sup>3</sup> (approx)
<b>Application Temp</b>	5°C to 35°C
<b>Service Temp</b>	-30 to 100°C.
<b>Shear Adhesion (typical)</b>	9kN (wet shear)
<b>Open Time</b>	30 - 40 mins @20°C
<b>Bed Thickness</b>	3-6mm
<b>Setting Time</b>	24-72 hours (depending on substrate).
<b>Specification</b>	BS5980 as a Type 2 Class AA adhesive
<b>Coverage</b>	One litre will fix and grout approx. 1m <sup>2</sup> of tiling depending on size of tile.

### Health & Safety

Consult MSDS for full list of hazards.

### Storage

Store at moderate temperatures. PROTECT FROM FROST

### Shelf Life

Minimum 12 months when stored according to manufacturer's instructions.

*The technical data contained herein is based on our present knowledge and experience and we cannot be held liable for any errors, inaccuracies, omissions or editorial failings that result from technological changes or research between the date of issue of this document and the date the product is acquired. Before using the product, the user should carry out any necessary tests in order to ensure that the product is suitable for the intended application. Moreover, all users should contact the seller or the manufacturer of the product for additional technical information concerning its use if they think that the information in their possession needs to be clarified in any way, whether for normal use or a specific application of our product. Our guarantee applies within the context of the statutory regulations and provisions in force, current professional standards and in accordance with the stipulations set out in our general sales conditions. The information detailed in the present technical data sheet is given by way of indication and is not exhaustive. The same applies to any information provided verbally by telephone to any prospective or existing customer.*