



Type



Customize



Print



Stick

Super fast & easy  
Just type, customize, print, stick

[www.dymo.com](http://www.dymo.com)



Features		LM 450D
<b>PRINTING</b>	Resolution	180 dpi
<b>FONT, STYLES &amp; EFFECTS</b>	Number of fonts	7
	Normal / Bold / Vertical / Outline / Shadow / Italic / Mirror / 3D / Strikethrough	✓
	Underline	✓
	Box	5+1*
	Number of character sizes	6
	Number of print lines	5 (on 24 mm)
	<b>MEMORY</b>	Last label
	Number of extra memories	10
	Last labels printed	15
<b>SOFTWARE</b>	Barcodes	✓
	Date & time	✓
	Incremental printing	✓
<b>TAPE CUT</b>	Automatic	✓
<b>POWER</b>	Adapter	✓
	Number of batteries	6
	Battery type	AA
<b>PC/MAC CONNECTABLE</b>		✓

\* Big font – only capitals, no accents or boxes

### Available tapes for LabelManager 450D



#### STANDARD D1 LABELS

<b>BLACK • CLEAR</b> 6/9/12/19/24 mm	<b>BLACK • WHITE</b> 6/9/12/19/24 mm	<b>BLACK • BLUE</b> 9/12/19/24 mm
<b>BLUE • CLEAR</b> 12 mm	<b>BLUE • WHITE</b> 9/12/19/24 mm	<b>BLACK • RED</b> 9/12/19/24 mm
<b>RED • CLEAR</b> 12 mm	<b>RED • WHITE</b> 9/12/19/24 mm	<b>BLACK • YELLOW</b> 6/9/12/19/24 mm
<b>WHITE • CLEAR</b> 12/19/24 mm	<b>WHITE • BLACK</b> 12/19/24 mm	<b>BLACK • GREEN</b> 9/12/19/24 mm

#### D1 PERMANENT LABELS

<b>BLACK • WHITE</b> 12/19 mm
----------------------------------

#### D1 FLEXIBLE LABELS FOR CURVED SURFACES

<b>BLACK • WHITE</b> 12/19 mm
----------------------------------

Dealer

50820080



Produced by: DYMO bvba - Industriepark-Noord 30 - B-9100 Sint-Niklaas - Belgium  
A Division of Newell Rubbermaid - [www.sanfordbrands.com](http://www.sanfordbrands.com)  
Made in Belgium - © 2007 DYMO

## LabelManager 450D

Create any label you need, stand alone  
or from your PC/Mac



# LabelManager 450D

The Labelmanager 450D brings a new dimension to high-performance labeling and to your desktop, with unmatched functionality, ease of use and versatility. The champion of desktop label makers can be used on its own or with your PC/Mac using DYMO software, which enables you to import barcodes, logos, graphics and typefaces.



## THE LABEL MAKER WITH YOU IN MIND

The labelManager 450D uses whisper-quiet thermal transfer print technology with a wide range of state-of-the-art features, including automatic cutting, spacious semi-graphical display and memory to help create labels faster and easier.

## QUICK GLANCE LABEL MAKER FEATURES

- PC/Mac connected via USB with a simple interface offering a full set of on-screen editing options and importing of logos, graphics and typefaces
- Full label customization with 7 fonts, 5 heights, 13 styles, 6 boxes, several background patterns and 6 types of barcodes
- Special "format break" function makes it simple to combine different labeling features on a single label for a unique look

