


## 104 Series

### S - Shielded

Shielded cable clamp with spacer and sleeve.



Cable dia. Range	Collet Ø	Cable Clamp Set <sup>1)</sup> PEEK or PBT Insulator	
		Plug	Receptacle
2.9 - 4.0	4.0	E3 104.3/4.0 + B	E3 104.4/4.0 + C
4.0 - 4.7	4.7	E3 104.3/4.7 + B	E3 104.4/4.7 + C
4.7 - 5.7	5.7	E3 104.3/5.7 + B	E3 104.4/5.7 + C

Cable dia. Range	Collet Ø	Cable Clamp Set <sup>1)</sup> PEEK or PBT Insulator	
		Plug	Receptacle
5.7 - 6.7	6.7	E3 104.3/6.7 + B	E3 104.4/6.7 + C
6.7 - 7.7	7.7	E3 104.3/7.7 + B	E3 104.4/7.7 + C
7.7 - 8.7	8.7	E3 104.3/8.7 + B	E3 104.4/8.7 + C
8.7 - 9.1	9.1	E3 104.3/9.1 + B	E3 104.4/9.1 + C

### U - Unshielded

Unshielded, one-piece cable clamp.




Cable dia. Range	Collet Ø	Cable Clamp Set <sup>1)</sup> PEEK or PBT Insulator
3.2 - 4.2	4.2	E3 104.6/4.2
4.2 - 4.7	4.7	E3 104.6/4.7
4.7 - 5.7	5.7	E3 104.6/5.7
5.7 - 6.7	6.7	E3 104.6/6.7

Cable dia. Range	Collet Ø	Cable Clamp Set <sup>1)</sup> PEEK or PBT Insulator
6.7 - 7.7	7.7	E3 104.6/7.7
7.7 - 8.2	8.2	E3 104.6/8.2
8.2 - 8.7	8.7	E3 104.6/8.7

### E - Environmental

Environmentally sealed clamp for use with shielded or unshielded cables.



Cable dia. Range	Collet Ø	Cable Clamp Set <sup>1)</sup> PEEK or PBT Insulator	
		Plug	Receptacle
2.9 - 4.0	4.0	E3 104.2/4.0 + B	E3 104.2/4.0 + C
4.0 - 4.7	4.7	E3 104.2/4.7 + B	E3 104.2/4.7 + C
4.7 - 5.7	5.7	E3 104.2/5.7 + B	E3 104.2/5.7 + C

Cable dia. Range	Collet Ø	Cable Clamp Set <sup>1)</sup> PEEK or PBT Insulator	
		Plug	Receptacle
5.7 - 6.7	6.7	E3 104.2/6.7 + B	E3 104.2/6.7 + C
6.7 - 7.7	7.7	E3 104.2/7.7 + B	E3 104.2/7.7 + C
7.7 - 8.7	8.7	E3 104.2/8.7 + B	E3 104.2/8.7 + C

<sup>1)</sup> For ordering information see Page 4-11-1.