

# A130 HSS Morse Taper Shank Drills

Metric

493752

Size (mm)	Flute Length (mm)	Overall Length (mm)	Morse Taper	Order Code	Price Each
2.50	30	111	1	023-441	
3.00	33	114	1	023-443	
4.00	43	123	1	023-447	
4.50	47	128	1	023-449	
5.00	52	133	1	023-452	
5.20	52	133	1	223-345	
5.50	57	138	1	023-454	
5.75	57	138	1	023-455	
6.00	57	138	1	147-7396	
6.50	63	144	1	147-7397	
7.00	69	150	1	023-460	
7.50	69	150	1	147-7398	
8.00	75	156	1	147-7399	
9.00	81	162	1	147-7400	
9.50	81	162	1	147-7401	
10.00	87	168	1	023-472	
10.30	87	168	1	223-360B	
10.50	87	168	1	147-7402	
11.00	94	175	1	147-7403	
11.50	94	175	1	147-7404	
12.00	101	182	1	147-7405	
13.00	101	182	1	147-7406	
13.25	108	189	1	023-484	
13.50	108	189	1	147-7408	
13.75	108	189	1	023-486	
14.00	108	189	1	147-7410	
14.25	114	212	1	023-488	
14.50	114	212	2	147-7411	
15.00	114	212	2	147-7412	
15.25	120	218	2	023-492	
15.50	120	218	2	147-7413	
15.75	120	218	2	023-494	
16.00	120	218	2	147-7414	
16.25	125	223	2	023-496	
16.50	125	223	2	147-7415	
17.00	125	223	2	147-7416	
17.25	130	228	2	023-500	
17.50	130	228	2	147-7417	
17.75	130	228	2	023-502	
18.00	130	228	2	147-7418	
18.25	135	233	2	023-504	
18.50	135	233	2	023-505	
18.75	135	233	2	023-506	
19.00	135	233	2	147-7421	
19.25	140	238	2	023-508	
19.50	140	238	2	147-7422	
19.75	140	238	2	023-510	
20.00	140	238	2	147-7423	
20.25	145	243	2	023-512	
20.5	145	243	2	147-7424	
21	145	243	2	147-7425	
21.5	150	248	2	147-7426	
22	150	248	2	147-7427	
22.5	155	253	2	147-7428	
23	155	253	2	147-7429	
23.25	155	276	2	023-524	
23.5	155	276	3	147-7430	
24	160	281	3	147-7431	
24.5	160	281	3	147-7433	
25	160	281	3	147-7434	
26	165	286	3	147-7435	
26.5	165	286	3	023-537	
27	170	291	3	147-7436	
27.5	170	291	3	147-7437	
28	170	291	3	147-7438	
29	175	296	3	147-7439	
29.5	175	296	3	147-7440	
30	175	296	3	147-7441	
30.5	180	301	3	023-553	
31	180	301	3	023-555	
31.5	180	301	3	023-557	
32	185	334	4	147-7442	
33	185	334	4	023-561	
34	190	389	4	147-7443	
35	190	339	4	147-7445	
36	195	344	4	023-567	
37	195	344	4	023-569	
38	200	349	4	023-571	
39	200	349	4	023-573	
50	220	369	4	023-595	