



The 281-876 is a compact tool wallet kit populated with high quality tools for the smaller precision applications.

The 281-888 is a tool wallet kit with a very high density of carefully chosen tools suitable for most electronic applications.

**281-876 Contents:**

|  |         |  |         |
|--|---------|--|---------|
| <b>Screwdrivers/Trimmers</b>           |         | <b>Gripping/Spanners</b>                             |         |
| Potentiometer trimmers                 | 145-307 | Tweezers, pointed tip, straight, 120mm long          | 441-132 |
| Jewellers', 3 slot and Phillips 0,00,1 | 108-580 | Tweezers, round point, straight, 150mm long          | 441-200 |
| Slot, 100 5mm blade                    | 281-219 | Seizers, straight nosed, serrated jaw 150mm Long     | 202-710 |
| Slot, mains tester, 150/250V ac        | 108-753 | Snipe nose combination pliers                        | 263-576 |
| Phillips, 80mm blade No. 1 point       | 281-300 | Combination spanners ring/open, set of 6.5mm to 10mm | 105-965 |
| Pozidriv, 100mm blade No 2 point       | 281-396 | <b>Miscellaneous</b>                                 |         |
| <b>Cutting</b>                         |         | Torch  | 538-050 |
| Light duty side cutters                | 108-714 | Tool wallet  | 105-383 |
| Wire stripper/cutter                   | 440-759 |  |         |

**281-888 Contents:**

|   |         |   |          |
|---|---------|---|----------|
| <b>Screwdrivers/Trimmers</b>                      |         | Flat nose pliers                                      | 108-717  |
| Potentiometer trimmers set of 3                   | 145-507 | Combination pliers, 152mm long                        | 263-590  |
| Jewellers', 3 slot and phillips 0,00,1            | 108-580 | Crimp tool for red, blue, and yellow insulated crimps | 150-353  |
| Slot, 100 5mm blade                               | 281-219 | Adjustable spanner, 150mm long, 20mm opening          | 105-215  |
| Slot, 150 5mm blade                               | 281-232 | Combination Spanners, ring/open set of 6.5mm to 10mm  | 105-965  |
| Slot, mains tester, 150/250V ac                   | 108-753 | <b>Measuring/Marking</b>                              |          |
| Phillips, 80mm blade No. 1 point                  | 281-300 | 150mm steel rule, mm and decimal inches (1/10 ths)    | 443-268  |
| Pozidriv, 100mm blade No 2 point                  | 281-396 | 3m metric/imperial tape rule                          | 628-815  |
| <b>Cutting</b>                                    |         | <b>Soldering</b>                                      |          |
| Light duty side cutters                           | 108-714 | Solder dispenser                                      | 146-706  |
| Retractable blade knife, including 2 blades       | 610-045 | Tip tinner/cleaner                                    | 419-631  |
| Wire stripper/cutter                              | 440-759 | Desoldering gun, miniature                            | 143-916  |
| <b>Gripping/crimping/spanners</b>                 |         | <b>Miscellaneous</b>                                  |          |
| Tweezers, pointed tip, straight, 120mm long       | 441-132 | Inspection mirror, swivel head extension handle       | 724-6298 |
| Tweezers, round point, straight, 150mm long       | 441-200 | Torch   | 538-050  |
| Seizers, Straight nosed, serrated jaw, 152mm long | 202-710 | Tool wallet   | 105-384  |
| Snipe nose combination pliers                     | 263-576 |   |          |

**Note:** Tool kits and contents subject to design change.

TEE11X/222618,401947

| Order Code | Price Each |
|------------|------------|
| 281-876    |            |
| 281-888    |            |