

Heavy-Duty Cabinets



Heavy-Duty Cabinet
Model No. HD4824A
Cabinet with shelves only



Heavy-Duty Cabinet
Model No. HD4824B
Cabinet with shelves and bins



Heavy-Duty Cabinet
Model No. HD4824C
Cabinet with shelves, louvers, and bins



Heavy-Duty Cabinet
Model No. HD4824D
Cabinet with shelves, louvers, and bins



Heavy-Duty Cabinet
Model No. HD4824E
Cabinet with louvers



Heavy-Duty Cabinet
Model No. HD4824F
Cabinet with louvers

- Heavy-Duty Cabinets provide MAXIMUM protection of parts and equipment from dust, damage, and theft.
- Greater weight capacity than standard cabinet systems.
- Powder coat paint is resistant to cuts and scratches.
- Industrial strength lock and key ensure complete security.
- Available with optional yellow AkroBin packages for your unique storage requirements.
- Cabinets ship assembled, shelving and panels require installation.
- Shelves are adjustable on 2" centers allowing the flexibility of securely storing multiple sized objects.
- 6 standard configurations - Shelves, Louvered Panels, Combination with Bins.
- Removable louvered panels attach to solid steel back panel.
- 14-gauge steel construction.

Heavy Duty Cabinet 48"W x 24"D x 78"H

Model No.	Description	Bin Model No.	Bin Dimensions L x W x H	Qty. of Bins
HD4824A	Cabinet w/Shelves Only	-	-	-
HD4824B	Cabinet w/Shelves and Bins	30240YELLO	14 ³ / ₄ " x 8 ¹ / ₄ " x 7"	35
HD4824C	Cabinet w/Shelves, Louvers, and Bins	30240YELLO	14 ³ / ₄ " x 8 ¹ / ₄ " x 7"	35
		30220YELLO	7 ³ / ₈ " x 4 ¹ / ₈ " x 3"	80
HD4824D	Cabinet w/ Shelves, Louvers, and Bins	30240YELLO	14 ³ / ₄ " x 8 ¹ / ₄ " x 7"	20
		30220YELLO	7 ³ / ₈ " x 4 ¹ / ₈ " x 3"	80
HD4824E	Cabinet w/ Louvers	30220YELLO	7 ³ / ₈ " x 4 ¹ / ₈ " x 3"	160
		30230YELLO	10 ⁷ / ₈ " x 5 ¹ / ₂ " x 5"	24
		30240YELLO	14 ³ / ₄ " x 8 ¹ / ₄ " x 7"	20
		30235YELLO	10 ⁷ / ₈ " x 11" x 5"	12
HD4824F	Cabinet w/ Louvers	30220YELLO	7 ³ / ₈ " x 4 ¹ / ₈ " x 3"	160
		30230YELLO	10 ⁷ / ₈ " x 5 ¹ / ₂ " x 5"	48
		30240YELLO	14 ³ / ₄ " x 8 ¹ / ₄ " x 7"	20

Cabinet Accessories:

- **For use with Standard Cabinets only.**
- Easily convert large cabinets to mobile units!
- Bin Cabinet Dollies feature solid, powder-coated steel deck with 1.25" lip and welded corners.
- Heavy-Duty Tubular Push Handle is welded to a 13-gauge powder coated steel mounting plate.



Bin Cabinet Dolly



Heavy-Duty Tubular Push Handle

Bin Cabinet Dollies

Model No.	Description	Cart Dimensions L x W x H (inches)	Polyolefin Casters (inches)	Weight Capacity
AC803618M26	18 x 36 Bin Cabinet Dolly	36 ¹ / ₂ x 18 ¹ / ₂ x 5 ¹ / ₂	3 x 1 ¹ / ₄	1000 lbs.
AC803624M26	24 x 36 Bin Cabinet Dolly	36 ¹ / ₂ x 24 ¹ / ₂ x 7	3 x 1 ¹ / ₄	1000 lbs.

Heavy-Duty Tubular Push Handle

Model No.	Description
AC18HDL	Heavy-Duty Tubular Push Handle for 36" x 18" Bin Cabinets
AC24HDL	Heavy-Duty Tubular Push Handle for 36" x 24" Bin Cabinets