









ZB4BV063








ZB4BV04

Pilot Light Heads










Shape of Head	For Use with Body Comprising Light Module Type	Color of Lens	Catalog Number	
	PROTECTED LED® only	White Green Red Yellow Blue	ZB4BV013 ZB4BV033 ZB4BV043 ZB4BV053 ZB4BV063	
	PROTECTED LED only Fresnel (jeweled) lens	White Green Red Amber Blue	ZB4BV013S ZB4BV033S ZB4BV043S ZB4BV053S ZB4BV063S	
	For BA9s incandescent bulb, neon or LED only	White Green Red Yellow Blue Clear	ZB4BV01 ZB4BV03 ZB4BV04 ZB4BV05 ZB4BV06 ZB4BV07	
	For BA9s incandescent bulb, neon or LED Fresnel (jeweled) lens	White Green Red Amber Blue Clear	ZB4BV01S ZB4BV03S ZB4BV04S ZB4BV05S ZB4BV06S ZB4BV07S	

Complete Bodies (Mounting Collar + Light Module for BA9s Incandescent Bulb, Neon or LED)

Description	Light Source	Supply Voltage (V)	Catalog Number	
Screw clamp terminal connections				
Direct supply	BA9s bulb 2.4 W max. Not included ▲	≤ 250	ZB4BV6	
Direct supply	BA9s incandescent bulb included	24 v 2 Watt	ZB4BV624	
Direct supply	BA9s incandescent bulb included	120 v 2.4 Watt	ZB4BV6120	
Transformer type 1.2 VA, 6 V secondary	BA9s incandescent bulb included	110–120 Vac 50/60 Hz	ZB4BV3	
		230–240 Vac 50/60 Hz	ZB4BV4	
		400–50 Hz	ZB4BV5	
		440–480 Vac 60 Hz	ZB4BV8	
		550–600 Vac 60 Hz	ZB4BV9	

▲ Order bulb separately, see page 17-32.

Complete Bodies (Mounting Collar + Light Module with PROTECTED LED)

Light Source	Supply Voltage	Color of Light Source	Catalog Number	
Screw clamp terminal connections▲				
	12 Vac/dc	White Green Red Yellow Blue	ZB4BVJ1 ZB4BVJ3 ZB4BVJ4 ZB4BVJ5 ZB4BVJ6	
	24 Vac/dc	White Green Red Yellow Blue	ZB4VB1 ZB4VB3 ZB4VB4 ZB4VB5 ZB4VB6	
	24–120 Vac/dc	White Green Red Yellow Blue	ZB4VBG1 ZB4VBG3 ZB4VBG4 ZB4VBG5 ZB4VBG6	
	110–120 Vac	White Green Red Yellow Blue	ZB4VG1 ZB4VG3 ZB4VG4 ZB4VG5 ZB4VG6	
	Flashing 24 Vac/dc	White Green Red Yellow Blue	ZB4BV18B1 ZB4BV18B3 ZB4BV18B4 ZB4BV18B5 ZB4BV18B6	
	110–120 Vac	White Green Red Yellow Blue	ZB4BV18G1 ZB4BV18G3 ZB4BV18G4 ZB4BV18G5 ZB4BV18G6	

▲ For Quick-Connect version, add "3" to the end of the catalog number Example: ZB4BVJ13 (Quick-Connect size 1 x 0.250" or 2 x 0.110").

For additional information, reference Catalog #9001CT0001.