



Electronics

a vital part of your world

Find Answers:

Friday, 14 October, 2005

CATALOG

Cross Reference

- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

Home

e-bulletin newsletter
SUBSCRIBE NOW!
 click here

Soft Shell Connectors

↳ .163" Centerline, 600 V, 9.5 A max. (Mini Universal MATE-N-LOK)



172163-1



Active

Directive 2002/95/EC
Compliant

RoHS Compliant

(Corporate P/N: 172163-1)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ✦ General Info ✦ Sales Info ✦ Assembly Subcontractors 	<ul style="list-style-type: none"> ✦ Pricing ✦ Product Availability 	<ul style="list-style-type: none"> ✦ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

Searchable Features:

Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Processes:	Not relevant for lead free process
Product Type:	Housing
Connector Line:	Mini-Universal MATE-N-LOK
Number of Circuits:	15
Centerline, Matrix (mm [in]):	4.14 x 4.14 [.163 x .163]
Contact Layout:	Matrix
Housing Type:	Receptacle (Cap)
Mount:	Panel Mount
Gender:	Receptacle (Cap)

Other Properties:

RoHS/ELV Compliance History:	Always was RoHS compliant
Contact Diameter (mm [in]):	0.99 [0.039]
Voltage (VAC):	600
CompactPCI:	No
Housing Flammability Rating:	UL 94V-0

Packaging Method:	One Piece Housing
Housing Material:	Nylon
Color:	Natural
Lock Type:	Positive Lock

[Copyright and Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]

.