



Electronics

a vital part of your world

Find Answers:

Saturday, 15 October, 2005

CATALOG

Cross Reference

- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

Home

e-bulletin newsletter  
**SUBSCRIBE NOW!**  
 click here

Soft Shell Connectors

↳ 5mm (.197") Centerline, 600 V, 14 A max. (Metrimate)

**AMP** 207304-1 Active

**Directive 2002/95/EC Compliant**

RoHS Compliant

(Corporate P/N: 207304-1)

[CAD Geometry](#) | [Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> <li>General Info</li> <li>Sales Info</li> <li>Assembly Subcontractors</li> </ul>	<ul style="list-style-type: none"> <li>Pricing</li> <li>Product Availability</li> </ul>	<ul style="list-style-type: none"> <li>Tooling</li> </ul>

**Photos & Line Drawings** - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

Searchable Features:

Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Processes:	Not relevant for lead free process
Product Type:	Housing
Connector Configuration:	Square Grid
Number of Positions:	24
Gender:	Plug
Coaxial Socket:	Without
Keyed:	No
Mount:	Free Hanging, Panel Mount
Mounting Ears:	Without

Other Properties:

RoHS/ELV Compliance History:	Always was RoHS compliant
Mating Polarization Method:	Polarizing Tab
Mating Connector Lock Type:	Locking Latch
Voltage (VAC):	600
Housing Material:	Thermoplastic
Housing Color:	Red
Housing Flammability Rating:	UL 94V-0
Packaging Quantity:	25

<b>Centerline (mm [in]):</b>	5.00 [0.197]
<b>Mating Connector Lock:</b>	With
<b>Jackscrew:</b>	Without
<b>8/32 Insert:</b>	No
<b>PCB Retention Feature:</b>	No

[Copyright and Privacy Statement](#)  
Visit [Tyco International Ltd.](#)

[ [Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#) ]

.