



Electronics

a vital part of your world

Find Answers:

Wednesday, 16 November, 2005

CATALOG

Cross Reference

- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

Home

e-bulletin newsletter  
**SUBSCRIBE NOW!**  
 click here

Multimate Contacts

Multimate

**AMP** 213843-4 Active

Directive 2002/95/EC Compliant

RoHS Compliant

(Corporate P/N: 213843-4)

[CAD Geometry](#) | [Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> <li>General Info</li> <li>Sales Info</li> <li>Assembly Subcontractors</li> </ul>	<ul style="list-style-type: none"> <li>Pricing &amp; Availability</li> </ul>	<ul style="list-style-type: none"> <li>Tooling</li> </ul>

Searchable Features:	
Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Processes:	Not relevant for lead free process
Pin/Socket:	Socket
High Current:	No
Contact Mating Area Plating:	Gold (30)
Wire Range (mm [AWG]):	8-5 <sup>2</sup> [10-8]
Contact Material:	Copper
Termination End Plating:	Gold Flash
Product Type:	.125 POWERBAND Contact
Contact Size:	8
Contact Type:	Power
Terminate To:	Wire

Other Properties:	
Test Current (Amps.):	50.0
Retention Clip:	With
Grade:	Commercial
Retention Clip Material:	Phosphor-Bronze
Retention Clip Plating:	Nickel

<b><a href="#">Insulation Support:</a></b>	Yes
<b><a href="#">Wire Termination Type:</a></b>	Crimp
<b><a href="#">Packaging Method:</a></b>	Loose Piece

[Copyright](#) and [Privacy Statement](#)  
Visit [Tyco International Ltd.](#)

[ [Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#) ]