



SHOCK RESISTANT

Shock resistant mobile hard drive, survives bumps and drops.



USB 3.0 & USB 2.0

CONNECTS TO ANY USB PORT



POWER VIA USB PORT

NO POWER ADAPTER NEEDED



INTEGRATED USB 3.0 CABLE

NO ADDITIONAL CABLES NEEDED



TOUGH DRIVE 3.0

SHOCK RESISTANT MOBILE HARD DRIVE / 2.5" / USB 3.0

THE TOUGHEST DRIVE THERE IS!

In today's world mobility has become a key factor. People who are on the road carry their whole office with them. Notebook, mobile phone, PDA, external hard drive... Imagine what can happen when you're late for a flight, running to the gate, and your external hard drive accidentally falls from your notebook case or out of your jacket pocket onto the floor... it breaks. Hundreds of hours of work, gigabytes of spreadsheets, documents, photo's... all gone. Not anymore! Freecom introduces the ToughDrive. The ideal external storage solution for people on the move. Fitted with an internal anti-shock frame and a unique soft silicone cover, it can withstand bumps and drops so your drive is still fully functional after it has dropped. The ToughDrive ensures you can still access your valuable files. A safe feeling. Provided by Freecom.

FREecom TOUGH DRIVE

- Durable, soft silicone cover, ideal for mobile computing
- Internal anti-shock mechanism insulating the hard drive from shock
- USB 3.0 for super fast data transfer – also connects to USB 2.0
- Integrated USB cable, no extra connection cables needed!
- Power via USB port, no power adapter needed
- Software included: Nero BackitUp & Burn, Green button energy saver and Password Protection
- The easiest way to add extra storage capacity to your computer
- High quality, slimline design
- No fan - no noise
- All Freecom devices meet the highest industry standards
- Two years manufacturers warranty and unlimited helpdesk support

DESIGNED FOR

- DATA STORAGE - Use all your data, like business information, digital photos, videos, MP3s and withstand bouncing around in handbags, cars etc.
- FILE SHARING - Share all your important data between computers and networks
- BACKUP - Protect all your data against calamity, human errors and viruses
- ARCHIVING - Archive all your data and lock up drive for extra data security
- INSTALLATIONS - Copy all your software on multiple PCs

A HARD NUT TO CRACK

Back up your important files with the strongest mobile drive there is: Freecom's ToughDrive. Rely on the ToughDrive and take it with you when you're on the road. Protected from inside out – you can protect your files with a password and the drive is tough enough to survive those daily bumps and drops.



JUST DROP IT

Just drop Freecom's ToughDrive. Thanks to the internal anti-shock mechanism, your files are safe and always super secured. The ruggedness of this drive is legendary and has been recognised and awarded many times by leading international computer magazines such as Chip, Computer!Total, C'T.



WHERE'S MY USB CABLE?

Have you ever forgotten your USB cable and been unable to connect your hard drive? This will never happen to you again thanks to the ToughDrive's unique integrated USB cable. Connect your ToughDrive to every computer, notebook or netbook wherever you are.



14 cm
8.3 cm
1.9 cm

FREECOM QUALITY

Since 1989 Freecom stands for creating innovative and professional digital (storage) solutions. All Freecom products are designed, engineered and certified in Germany according to the highest quality standards to guarantee customer satisfaction. Our in-house technical development process, the use of the highest quality components and German product inspection standards ensure superior quality and reliability. To meet the high expectations of professional users Freecom products are delivered with extensive warranty and unlimited free helpdesk support.

WHAT WILL IT HOLD	320GB	500GB	640GB	750GB	1TB
MP3 songs	64.000	100.000	128.000	150.000	200.000
JPEG pictures	213.333	333.333	426.666	500.000	680.000
DVD movies	72	111	144	166	220
DivX/Xvid movies	320	500	640	750	1.000

Definitions: 1GB = 1000MB - 1MP3 song = appr. 5MB / 1 JPG photo = appr. 1.5MB / 1 DivX/Xvid movie = appr. 1GB / 1 DVD movie = appr. 4.5GB

PRODUCT SPECIFICATIONS

- CAPACITY:** 500GB, 1TB
- INTERFACE:** USB 3.0, also connects to USB 2.0*
- HARD DRIVE TYPE:** 2.5" SATA, low noise, low power consumption
- DATA TRANSFER SPEED:** max. 5000 Mbit/s (USB 3.0), theoretical maximum data transfer speed
- POWER REQUIREMENTS:** power via USB port, no power adapter required
- MTBF:** 50.000 POH
- ENCLOSURE:** silicone
- DIMENSIONS:** 14 x 8.3 x 1.9 cm
- WEIGHT:** 200 g
- ENVIRONMENTAL SPECIFICATIONS:**
 Operating temperature: 10° C / 35° C
 Storage temperature: -20° C / 70° C

MINIMUM SYSTEM REQUIREMENTS

PC: Intel Pentium III / AMD Duron 900 MHz or higher, 256MB RAM (Vista: 512MB RAM) or higher, available USB 3.0 or USB 2.0* port, Windows XP / Vista / 7
MAC: PowerPC G3/G4/G5, Power Book G3/G4 or Intel Mac, 256MB RAM or higher, available USB 2.0 port*, Mac OS X v10.4.8 or higher

* When connected to USB 2.0, the data transfer speed will be according to USB 2.0 specification.

PACKAGE INCLUDES

- Freecom ToughDrive 3.0
- Integrated USB 3.0 connection cable
- USB extension cable
- Quick Install Guide
- Free unlimited helpdesk support
- Two years manufacturer's warranty

REV1 137/14092011/PWCH

TOUGH DRIVE 3.0	500GB	1TB
Art.-Nr.	56058	56057
EAN-Code	4021801560582	4021801560575
Colour	Dark Grey	Dark Grey