


TubeSleeve Carriers

Brady TubeSleeve Carriers are the ideal complement to self-laminating labels, where the cables are thin and available space for text is small. Apply the tubesleeve to the cable and then apply the self-lam. The limited available space is increased significantly, giving you the possibility of printing more text.



Order Reference	Min. Cable Diam (mm)	Max. Cable Diam (mm)	Recommended Label
BTS1426	1	4	PTL-31-427
BTS4626	4	6	PTL-31-427
BTS6826	6	8	PTL-23-427
BTS81226	8	12	PTL-23-427



PTLFP-01-425



PTLFT-01-425

Fibre Optic Labels (B-425), Flag

Polypropylene (B-425)

Diagram	Order Reference	Label Dimensions Labels Per Roll	A (mm)	B (mm)	Applications	Maximum Characters Per Line For Font: 2	Maximum Lines Of Text For Font: 2
▲	PTLFP-01-425	250	30.00	10.00	Pig-Tail and Single Fibre ID	26	3
▼	PTLFT-01-425	250	30.00	10.00	Pig-Tail and Single Fibre ID	26	3

Workstation Labels

B-412 Polypropylene,
B-422 Permanent Glossy Polyester,
B-430 Clear Polyester




Diagram	Order Reference	Labels Per Roll	Label Dimensions A (mm)	B (mm)	Applications	Maximum Characters Per Line For Font: 2	Maximum Lines Of Text For Font: 2
▲	PTL-7-422	500	12.70	12.70	1-6 Outlet Faceplates	11	5
▲	PTL-7-430	500	12.70	12.70	1-6 Outlet Faceplates	11	5
▲	PTL-16-422	500	25.40	9.52	1-4 Outlet Faceplates	24	3
▲	PTL-16-430	500	25.40	9.52	1-4 Outlet Faceplates	24	3
▲	PTL-17-422	500	25.40	12.70	1-4 Outlet Faceplates	24	5
▲	PTL-17-430	500	25.40	12.70	1-4 Outlet Faceplates	24	5
▲	PTL-29-422	500	38.10	12.70	1-2 Outlet Faceplates	37	5
▲	PTL-29-430	500	38.10	12.70	1-2 Outlet Faceplates	37	5
▲	PTL-39-422	750	9.52	15.24	1-6 Outlet Faceplates	8	6
▲	PTL-39-430	750	9.52	15.24	1-6 Outlet Faceplates	8	6
▼	PTL-40-412	750	49.23	9.52	Faceplates with DESI-STRIP	40	3
▼	BPTL-40-412	5 000	49.23	9.52	Faceplates with DESI-STRIP	40	3
▲	PTL-44-422	500	12.70	9.52	1-6 Outlet Faceplates	11	3
▲	PTL-44-430	500	12.70	9.52	1-6 Outlet Faceplates	11	3
▲	PTL-45-422	500	38.10	9.52	1-2 Outlet Faceplates	37	3
▲	PTL-45-430	500	38.10	9.52	1-2 Outlet Faceplates	37	3
▲	PTL-68-430	750	6.10	3.81	Siemens Faceplates	4	2
▲	PTL-69-430	750	13.46	3.81	Siemens Faceplates	11	2
▲	PTL-70-430	750	6.10	5.08	Siemens Faceplates	4	2
▲	PTL-71-430	750	6.10	5.08	Siemens Faceplates	7	2
▲	PTL-85-430	750	18.80	6.10	Siemens Faceplates	17	2
▲	PTL-99-430	750	18.80	8.12	Siemens Faceplates	17	2