

ProCart™ Box-top? Flat-top? It's both.

Time saving. Smart working. Innovative.

Introducing the ProCart™: the first "double-duty" utility cart.

It's engineered to adapt to all the ways – and all the places – you work.

Flip its side gates down and the ProCart™ is a flat-top cart – perfect for sliding boxes on and off the shelves in the warehouse.

Quickly flip its side gates up and the ProCart™ is a box-top cart. Use it to securely transport cartons, medical supplies, or mixed items.

Adding our optional Rail System and AkroBins® (as shown), the ProCart™ becomes a customized, portable work center for the assembly line or warehouse.

It doesn't just look different. It is different!

Box-top to flat-top versatility

Quickly and easily convert the ProCart™ to a flat-top or a box-top cart with one hand. Hinged side gates on both shelves flip up or down for different cart configurations. Tools aren't needed for these conversions.

Reinforced construction

Built for years of rugged use, the ProCart™ is made of high-density polyethylene structural foam. The panels are dent-resistant, rust-proof, and never need painting.



Innovative I-beam design

Compared to ordinary "four post" carts, loading and unloading oversized boxes on the ProCart's lower shelf is a snap with this I-beam design, especially in narrow aisles. Rounded corners and edges also prevent mishaps.

The beige ProCart™ is perfect for healthcare facilities. Small and large models can be fitted with the Akro-Mils® nine-rail hanging system and AkroBins® to make medical supplies easily accessible.



Accessible supplies



The ProCart's deep, molded-in compartments keep your handheld computer, scanner, coffee mug* or other items within reach – yet secured – during transport. Comfortable, full-width handles give you complete handling control.
*Only large cart has mug holder.

Customized organization

Our optional nine-rail system and interchangeable AkroBins® (sold separately) offer the ultimate solution in organization and storage. Hundreds of different bin configurations make this option ideal for order picking or distributing department supplies.



Generous payload

Even under its 400-pound (180kg) maximum payload, the ProCart™ easily maneuvers around tight corners and through narrow aisles. Each shelf can hold a hefty 200 pounds (90kg).

Durable wheels

The ProCart™ glides on durable, non-marking, 5" wheels. Toe-touch, locking rear wheels stabilize the ProCart™ for loading or convert it to a portable workstation.




SPECS: ProCart™




1 - YEAR LIMITED WARRANTY
For information on our 1 - Year Limited Warranty or replacement components, call your Akro-Mils distributor.

Large Cart
Model No. 30936



Small Cart
Model No. 30930



ProCart Ordering Information

Model No.	Description	Dimensions		Color	Carton Quantity
		Inches	mm		
30936	Large cart	45L x 24W x 34 3/4H	1143 x 588 x 813	Gray/Beige	1
30930	Small cart	40L x 19 1/2W x 34 3/4H	1016 x 495 x 813	Gray/Beige	1

Easy Assembly – requires phillips screwdriver and rubber mallet

Available Colors

ProCart™				
AkroBins®				
Cabinet				

9-Rail Hanging System Ordering Information

The 9-Rail Hanging System is required to hang AkroBins® and modular cabinets on your ProCart™. For large cart, use Model No. 30906 – For small cart, use Model No. 30900



AkroBin® Ordering Information


To create a customized ProCart™ with AkroBins®, use the two charts below to determine the quantity of AkroBins® that will fit your need. Carts, rail kits, bins, cabinets and suspension straps must be ordered separately. When ordering, please specify red, yellow, blue, or stone colored bins.



Use this chart when ordering one size AkroBins® for your ProCart™

Bin Model No.	30210	30220	30224	30230	30234	30235	30239	30240	30250	30255
Bin Dimen. (L"xW"xH")	5 3/8 x 4 1/8 x 3	7 3/8 x 4 1/8 x 3	10 7/8 x 4 3/16 x 4	10 7/8 x 5 1/2 x 5	14 3/4 x 5 1/2 x 5	10 7/8 x 11 x 5	10 3/4 x 8 1/4 x 7	14 3/4 x 8 1/4 x 7	14 3/4 x 16 1/2 x 7	10 3/4 x 16 1/2 x 5
30936 (large cart)	80	80	48	36	36	18	16	16	8	12
30930 (small cart)	70	70	42	30		12	12			

Use this chart when ordering multiple sizes of AkroBins® or cabinets for your ProCart™. The following suggested options* are designed to maximize the efficiency of your ProCart™. Due to typical "full-case" purchasing requirements for AkroBins®, you may need to order more AkroBins® than would actually fit on the ProCart™.



Use this chart when ordering multiple sizes of AkroBins® or cabinets for your ProCart™

Bin Model No.	30210	30220	30224	30230	30234	30235	30239	30240	30250	30255	19909/Cabinet	98400 Suspension Straps
Large cart												
Option A		48		12								
Option B				24		6						
Option C						12				4		
Option D				32							4	4
Option E				18						6		
Small cart												
Option F		42		10								
Option G				10								
Option H		24									2	2