




Search for Tooling Product Feature Selector Contact Us About This Product English (C

Have a Ouestion? Chat with a Product Information Specialist

What can we help you find?

**Industries About TE Products** Resources **Support Center** My Account 📴 Share Email 🚞 Print 929990-1 Product Details Quick Links 1.5/2.5/4.0mm Pin Diameter **Connector System** Check Pricing & Availability







Always EU RoHS/ELV Compliant (Statement of

#### **Product Highlights:**

- Contact
- Product Series = 1.5 mm System
- Contact Type = Socket
- CuNiSi Contact Base Material
- Tin Contact Plating, Mating Area, Material

View all Features

Add to My Part List Request Sample Find Similar Products

**Buy Product** 

#### Documentation & Additional Information **Product Drawings: Additional Information:** DIA. 1.5 mm SOCKET CONTACT DIA.1.5 mm Buchsenkontakt (PDF, Product Line Information English) Related Products: Catalog Pages/Data Sheets: • Tooling None Available

Product Specifications: None Available

Application Specifications: None Available

## Instruction Sheets:

None Available

## CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version M5)
- 3D Model (IGES, Version M5)
- 3D Model (STEP, Version M5)

# List all Documents

## Product Features (Please use the Product Drawing for all design activity)

#### **Product Type Features:**

- <u>Product Type</u> = Contact
- <u>Product Series</u> = 1.5 mm System
- <u>Sealed</u> = Yes

## **Body Features:**

- Wire Range (mm [AWG]) = 1.00-2.50<sup>2</sup> [17-13]
- Single Seal Part No. = 828905-1

#### **Contact Features:**

- Contact Type = Socket
- Contact Base Material = CuNiSi
- Contact Plating, Mating Area, Material = Tin

## **Industry Standards:**

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

Accepts Wire Insulation Diameter, Range (mm [in]) = 2.21 - 3.00 [0.087 - 0.118]

## Packaging Features:

- <u>Packaging Method</u> = Strip
- Packaging Quantity = 3,800

### Other:

- GET 0.64 Connector System = No
- Brand = AMP

#### **Corporate Information Quick Links Customer Support** Who We Are Check Distributor Inventory Email or Chat With Us

Cross Reference Investors Find a Phone Number News Room Find Documents & Drawings Search Knowledge Base Supplier Portal Product Compliance Support Center Manage your Account