

**TRIM PLATE ADAPTERS**

Trim Plate Adapters made with steel and aluminum allow installation of 1/16 DIN and 1/8 DIN meters in larger existing panel cutouts.



**INF-BB/205-BB**

**BUMPER BAND® Protective Guards**

BUMPER BAND guards are made from a flexible material designed to provide additional moisture protection and protect against accidents. Available in 1/8 and 3/64 DIN sizes, BUMPER BAND guards are compatible with INFINITY® Series and INFINITY 'C' Series meters, as well as Model 205 meters. Guards are available in gray, yellow, black, blue, green, red, orange, purple and white.



**19" Rack Panels**



Mount either one, two, three or four 1/8 DIN meters in a standard 19" panel with RP panels. These panels are made from anodized aluminum.



**RJ to 9 or 25-PIN sub-D SERIAL PORT CONNECTORS**

25SC2 / 25SC4

9SC2 / 9SC4

Part Number	Description
TP4	Trim plate adapter to install 1/16 DIN meter in existing 1/4 DIN panel cutout
TP5	Trim plate adapter to install 1/8 DIN meter in existing 1/4 DIN panel cutout
TP6	Trim plate adapter to install 1/16 DIN meter in existing 1/8 DIN panel cutout
INF-BB-GY/N	1/8 DIN Gray
INF-BB-YL/N	1/8 DIN Yellow
INF-BB-BK/N	1/8 DIN Black
INF-BB-BL/N	1/8 DIN Blue
INF-BB-GR/N	1/8 DIN Green
INF-BB-RD/N	1/8 DIN Red
INF-BB-OR/N	1/8 DIN Orange
INF-BB-VL/N	1/8 DIN Purple
INF-BB-WH/N	1/8 DIN White
205-BB-YL/N	3/64 DIN Yellow
205-BB-BK/N	3/64 DIN Black
205-BB-BL/N	3/64 DIN Blue
205-BB-GR/N	3/64 DIN Green
205-BB-RD/N	3/64 DIN Red
205-BB-OR/N	3/64 DIN Orange
205-BB-VL/N	3/64 DIN Purple
205-BB-WH/N	3/64 DIN White
RP18	Single 1/8 DIN cutout
RP28	Two 1/8 DIN cutouts
RP38	Three 1/8 DIN cutouts
RP48	Four 1/8 DIN cutouts
RP23	Two 3/64 DIN cutouts
RP43	Four 3/64 DIN cutouts
9SC2	to 9-pin serial adapter for RS-232
9SC4	to 9-pin serial adapter for RS-485 or RS-422
25SC2	to 25-pin serial adapter for RS-232
25SC4	to 24-pin serial adapter for RS-485 or RS-422
SP1	male to two (2) RJ12 female for daisy chain of RS-485 or RS-422 networks