

## Studio Grade Coax Transport

## “Trompeter Inside” OEM Solutions


Straight printed circuit mount BNC jack connectors  
UCBJ224



Edge mount BNC jack connectors  
UCBJE20-x




Right angle BNC PC board mount connectors  
6-0001-2



## Total “Broadband Connectivity” System M4Flex

- Subpanel system for flexible mixed wireline termination/ routing
- Subpanel options:
  - Universal subpanel with BNC, F, RJ45, RCA, and SC keystone inserts
  - DDM-2 for wiring closet deployment of DS3 line rates
  - DDPM-2 with gas-tube protection for OSP deployment
- Panel enclosure options:
  - Lockable wall-mount enclosure- holds 4 subpanels
  - L-Bracket for interior wiring closet - holds 3 subpanels
  - 19” or 23” 1RU rack panel, holds 3-4 subpanels



## Trompeter

Connectivity Solutions  
5550 E. McDowell Road  
Mesa, AZ 85215  
USA  
+1 480 985 9000  
1 800 778 4401

[www.trompeter.com](http://www.trompeter.com)



**Trompeter**  
Connectivity Solutions

**EMERSON**  
Network Power

# Studio Grade Solutions

## Coaxial Patch Jacks

WECo Jack Family  
HDVDP

- normal-thru, self-terminating or straight-thru versions

MiniWECo Jack Family

HDVDPM

- normal-thru, self-terminating or straight-thru versions



## Loaded Panel

1RU WECo panel  
JSIB-48S/HDVDP

- 1 RU 19"



1RU Mini-WECo panel

JSMW64S/HDVDP

- 1 RU 19"



## Cable Assemblies

MiniWECo Patchcord

PCMWB-24



WECo Patchcord

PCW-24-75



BNC-BNC Patchcord

UPCYB-24-75



WECo-BNC Patchcord

UPCWX-24-75



## Studio Grade Connectors

UPL2000 Series BNC Connectors

UPL2000-xx

- HDTV capable, Full 1.485 Gbps, SMPTE 292M uncompressed signal levels
- Digital signal designed
- Gold Spring fingers
- Black coupling sleeve for superior electromagnetic signal management
- True 75 Ω



Carrier Class F Connectors

PL1305C-xx

- Classic 3 piece construction
- Trompeter industry standard installation tooling and training
- High Frequency capable
- Studio grade construction



PL11MW Series Patch Plug MiniWECo Connectors

PL115C-xxx


PL1WC Series Patch Plug WECo Connectors

PL1W-xxx

## Looping Plugs

MiniWECo looping plug

LPMWHF



WECo looping plug

LPW-75

## Tooling

TK2-17 Tool Kit

BCS/C24T3D

- Power coax stripping tools



## Adapters & Terminators

BNC 75Ω termination

UTNA2000



WECo patch plug to BNC adapter

- AD1WHD
- 75 Ω



MiniWECo patch plug to BNC adapter

ADMW12

1RU BNC feed-thru distribution panels

JSD3-48/UBJ228



WECo-BNC

J3W

- Single patch jack

MiniWECo-BNC

J11MW/J11MWL

- HD single patch jack available in regular & long



F to BNC Adapter

AD1300

- High Frequency cable
- Enabling conversions from F connectors to BNC
- Best in class choice for home theater conversion for studio grade performance

