



NBNC75P



BS-BNC

NEUTRIK BNC CONNECTORS: PUSH-PULL CABLE - HDTV

A range of high quality BNC connectors, giving excellent mechanical, electrical and assembly performance. Precision machined components give accurate impedance and excellent return-loss, even at high frequencies above 1GHz, suitable for HDTV, SDI (serial digital) and analogue video.

An extremely ergonomic 75 ohm cable connector with push-pull locking operation, for high density or rapid assembly installations such as patchbays or location equipment. The connector locks with a straight push on the shell and releases with a straight pull. Assembly is straightforward, as the centre pin may be soldered, or crimped (with any of the Neutrik BNC crimp jaws, except type Z - see "Neutrik BNC Connectors, Tools"). The cable is then held in place and the screen terminated with a cable retention clamp based on the Neutrik chuck principle (not crimped), popular on audio connectors.

Connector screen contacts are optimised for certain cable diameters. Connectors in sizes for popular cables are held in stock; versions for other cables are available to special order, please contact Technical Support. Colour-coded cable boots are available to identify cables and connectors.

Required accessories: A spanner incorporating a cable preparation guide is required to assemble push-pull connectors- see "Neutrik BNC Connectors, Tools".

Connector	Canford cables	Canare Cables	Other Cables crimp jaw	Centre-pin
NBNC75P-FE7	SDV, SDM		Belden 1855A, 1855ENH	Any Neutrik
NBNC75P-LS9		L-4CFB	Belden 1505A, 1505F	Any Neutrik
NBNC75P-NS7	VCS (PSF1/3)	LV-61S	RG59B/U	Any Neutrik
NBNC75P-VS11	SDV-L, SDV-F	L-5CFB	Belden 1694A	Any Neutrik

48-581	NEUTRIK BNC NBNC75PFE7 Male cable, push-pull, group X
48-582	NEUTRIK BNC NBNC75PLS9 Male cable, push-pull, groups Q1 & Q2, Canare L-4CFB
48-583	NEUTRIK BNC NBNC75PNS7 Male cable, push-pull, groups B, Q and Q1
48-584	NEUTRIK BNC NBNC75PVS11 Male cable, push-pull, group Y & Canare L-5CFB
48-590	NEUTRIK BNC BS-BNC-0 PUSH-PULL CABLE BOOT Black
48-591	NEUTRIK BNC BS-BNC-1 PUSH-PULL CABLE BOOT Brown
48-592	NEUTRIK BNC BS-BNC-2 PUSH-PULL CABLE BOOT Red
48-593	NEUTRIK BNC BS-BNC-3 PUSH-PULL CABLE BOOT Orange
48-594	NEUTRIK BNC BS-BNC-4 PUSH-PULL CABLE BOOT Yellow
48-595	NEUTRIK BNC BS-BNC-5 PUSH-PULL CABLE BOOT Green
48-596	NEUTRIK BNC BS-BNC-6 PUSH-PULL CABLE BOOT Blue
48-597	NEUTRIK BNC BS-BNC-7 PUSH-PULL CABLE BOOT Violet
48-598	NEUTRIK BNC BS-BNC-8 PUSH-PULL CABLE BOOT Grey
48-599	NEUTRIK BNC BS-BNC-9 PUSH-PULL CABLE BOOT White

UK Sales - tel 0191 418 1122
 fax 0191 418 1123
 sales@canford.co.uk

International Sales - tel +44 191 418 1133
 fax +44 191 418 1134
 international@canford.co.uk

Tech Support - tel 0191 418 1144
 fax 0191 418 1145
 techsupport@canford.co.uk