




PRODUCT SPECIFICATION

Brand	C.K
Product Range	Rules
Catalogue number	3510, 3530 & 3531
Date	04/03/2008

Range Description Rules in wood and metal				
Features				
<p>3510</p> <ul style="list-style-type: none"> Professional quality construction with heavy brass hinges and ends 4 fold for compact storage Metric graduations at 5mm intervals on the top edge and 1mm on the bottom edge Imperial graduations at 1" on the top edge and 1/8" on the bottom edge 		 <p>3510</p>		
<p>3530</p> <ul style="list-style-type: none"> Stainless steel for long life Hanging hole for storage Metric graduations at 0.5 and 1mm intervals Imperial graduations at 1/64", 1/32" and 1/16" intervals 				
<p>3531</p> <ul style="list-style-type: none"> For convenient cutting measuring and marking Strong anodized Aluminium blade with tough plastic handle Hanging hole for storage Metric graduations at 1mm intervals 				
		 <p>3530</p>		
		 <p>3531</p>		
Item Number	Item Description	EAN No	Commodity code	Carton Qty
T3510	Folding wooden rule 1000mm/3ft	5013969479003	90178010	6
T3530 06	Steel rule 150mm/6"	5013969480504	90178010	6
T3530 12	Steel rule 300mm/12"	5013969480603	90178010	6
T3531	Straight edge rule 1000mm	5013969020427	90178101	1

Technical product information	
Standards compliance	
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K products are guaranteed for life against imperfect materials or workmanship
Country of origin	3510 – UK 3530 – Germany 3531 – Slovenia

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3510	35	10	60	106	50	11	315	116
T3530 06	17	1	166	10	43	1	225	18
T3530 12	27	1	323	70	63	1	390	84
T3531	60	110	60	655	60	110	60	670

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T3510	65	900	50	754		
T3530 06	100	4	240	112		
T3530 12	150	4	430	518		
T3531						

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T3510	10	Wallet					58	Box
T3530 06	8	Wallet			4	Bag		
T3530 12	14	Wallet			14	Bag		
T3531	15	Wrapping						