

**Thomas & Betts**

***Factory-Mounted Old Work Swing Ears  
Save You Time on the Job Site!***

***Steel City***<sup>®</sup>

4"-Square Old  
Work Box with  
Swing Ears



Swing Ears with  
Self-Threading  
Screws May  
Be Purchased  
Separately





# Steel City®

## 52171-OW 4"-Square Old Work Box with Swing Ears



### Swing Ears Provide Behind-the-Wall Gripping Force

Save time on the job site with the Steel City 4"-Square Old Work Box with Swing Ears. Swing ears, which keep the box securely fastened in place after installation, come premounted for a faster install and can be used on walls up to 3/4" thick. Swing ears (OW SWING EAR) can also be purchased separately for field installation. These come packaged in plastic bags containing a pair of swing ears with two self-threading screws for each ear. No tapping required — just mount directly to a Steel City Welded Box. Welded boxes (excluding the 4 1/16" box) come standard with the appropriate punched side-panel holes for the OW SWING EAR.



### Makes installation fast and easy!

- Insert box into new or existing cut-out in wall
  - Use slotted or Phillips screwdriver to turn ear screws
  - Swing arm will tighten against wall, securing box firmly in place
- 
- Ideal for old work or retrofit applications in hospitals, schools, fire-alarm installations, and any other environment in which Steel City 4"-square boxes must be added or replaced in existing walls
  - 52171-OW is a 4"W x 4"H x 2 1/8"D metallic box with eccentric knockouts consisting of catalog numbers 521711234E and OW SWING EAR
  - Old work swing ears factory-mounted to box
  - For wall thicknesses up to 3/4"
  - Swing-ear mechanism easily turned with slotted or Phillips screwdriver for quick, simple installation
  - OW SWING EAR also sold separately for field installation (packaged in pairs with self-threading screws)

### 4"-Square Old Work Box with Swing Ears

Cat. Number	Description	Std. Pkg. Qty.	UPC Number
52171-OW	Metallic 4"-Sq. x 2 1/8"D Old Work Box with Factory-Mounted Swing Ears	25	78599103740
OW SWING EAR	Swing Ears Only (for field installation) with Self-Threading Screws	50 (25 pair)	78599104044



Please ask your Thomas & Betts sales representative for a complete catalog of quality Thomas & Betts electrical products or visit us at [www.tnb.com](http://www.tnb.com). For customer service, call 1-800-816-7809. For technical questions, call 1-888-862-3289.

**Thomas & Betts Corporation**  
Electrical Division  
8155 T&B Boulevard  
Memphis, TN 38125  
901-252-5000

**Thomas & Betts Ltd.**  
700 Thomas Avenue  
Iberville, Québec J2X 2M9  
450-347-5318