


PRINTS VARIOUS COLOURS



LAMINATED TAPE				
CHARACTER COLOUR	BASE COLOUR	12mm	9mm	6mm
BLACK	CLEAR	TZ-131	TZ-121	TZ-111
	CLEAR (MATT)	TZ-M31		
	SILVER (MATT)	TZ-M931		
	WHITE	TZ-231	TZ-221	TZ-211
	RED	TZ-431	TZ-421	
	BLUE	TZ-531	TZ-521	
	YELLOW	TZ-631	TZ-621	TZ-611
	GREEN	TZ-731	TZ-721	
	FLU. YELLOW	TZ-C31		
	FLU. ORANGE	TZ-B31		
RED	CLEAR	TZ-132	TZ-122	
	WHITE	TZ-232	TZ-222	
BLUE	CLEAR	TZ-133	TZ-123	
	WHITE	TZ-233	TZ-223	
GOLD	BLACK	TZ-334	TZ-324	
	BLACK	TZ-335	TZ-325	
WHITE	RED	TZ-435		
	BLUE	TZ-535		
	ORANGE	TZ-635		
	GREEN	TZ-735		
	CLEAR	TZ-135		
STRONG ADHESIVE TAPE-LAMINATED				
BLACK	WHITE	TZ-S231	TZ-S221	TZ-S211
FLEXIBLE ID TAPE-LAMINATED				
BLACK	WHITE	TZ-FX231	TZ-FX221	TZ-FX211
	CLEAR	TZ-FX131	TZ-FX121	TZ-FX111
	YELLOW	TZ-FX631	TZ-FX621	TZ-FX611
IRON ON FABRIC TAPE				
BLUE	WHITE	TZ-FA3		
	BLUE	TZ-FA53		
	YELLOW	TZ-FA63		
	PINK	TZ-FAE3		


All tapes are 8m except fluorescent tape (5m) and iron-on fabric tape (3m). Some kinds of tapes are not available in some countries. The actual tape colour may vary from above.

P-touch 1000

Longer Lasting Labels

Brother's unique, patented TZ tapes are designed to be extra hard wearing. Tests have shown that these scratch-proof labels can withstand heavy abrasion, electrical resistance and lengthy exposure to chemicals, sunlight, water and extreme temperatures from -50°C to 300°C. Brother laminated tapes consist of six layers of materials, resulting in a thin, extremely strong label. Characters formed with thermal transfer ink are actually printed onto the underside of the laminate. Sandwiched between two layers of PET (polyester film) this lets you create characters that are virtually indestructible.

Brother Laminate Tape Construction



Tape Options

- Options include standard laminated tape including Fluorescent and Transparent options. Specialist tapes include Matt, Strong Adhesive, Flexible ID, and Iron-on fabric. Available in varying widths, character and tape colour options.

Tape Widths



Contact:

brother At your side.

Brother International (Aust) Pty Ltd

Corporate Web-site: www.brother.com.au Technical Web site: <http://solutions.brother.com>
NSW/ACT: 7 Khartoum Rd. North Ryde NSW 2113 Phone: (02) 9887 4344 Fax: (02) 9870 7234
VIC: 43 Carrington Rd. Box Hill VIC 3128 Phone: (03) 9899 4844 Fax: (03) 9899 4833
QLD/NT: Unit 4, 57 Miller St. Murrarie QLD 4172 Phone: (07) 3348 9266 Fax: (07) 3348 9366
SA/TAS: Unit 4, 13 King William Rd. Unley SA 5061 Phone: (08) 8272 1300 Fax: (08) 8272 1199
WA: 117 Great Eastern Highway. Belmont WA 6104 Phone: (08) 9478 1955 Fax: (08) 9277 2177
 All specifications subject to change without notice

At your side.
brother

P-touch
1000

Electronic labeller



Brother | P-touch 1000

P-touch 1000

Technical Information

Hardware

Housing Dimensions	108mm(W) x 196mm(D) x 55mm(H) (with cutter lever)
Housing Design	Slim Handheld
Housing Weight	335g (without batteries and tape cassette)
Number of Keys	49 keys
Power (not included)	AAA sized Alkaline Batteries x 6pcs or AC Adapter (AD-5000)
LCD	8 chrs x 1 line
Item Included	Users Guide 12mm x 5m Black on White Starter Tape
Tape Type	TZ-tape
Tape Width Size	6 / 9 / 12mm
Print Head	180 dpi
Max. Print Height	9mm

Firmware

Built in Fonts	Helsinki & Oklahoma
Characters	241
Symbols	59
No. of lines printable	Max. 2 lines
Text Buffer	55 characters
Memory	Yes (Store,/Recall,/Delete) up to 9 files, Max 300 characters
Type Styles	Normal / Bold / Outline / Shadow / Italic Italic Bold / Italic Outline / Italic Shadow / Vertical / Mirror
Framing & Fill Pattern	5 kinds (Off/Unfl/Round/Banner/Wooden/Vine)
Repeat Printing	Yes (1-9)
Underline	Yes
Tape Margin Settings	Yes (Full/Half/Narrow/Chain)
Numbering	Yes (0-9)
Battery Weak Indication	Yes
Auto Power Off	Yes
Print Image (Preview)	Yes



Always at your side

Preview screen enables you to check your label before you decide to print

Separate ABC 123 keys simple, clear keyboard makes it so easy to use

Powered by AC adapter for even greater economy
or
6 x AAA batteries, (neither included)

Shortcut Feature save time when formatting your labels

Slim hand-held design a stylish machine that is light yet durable

Manual built-in cutter – every label is cut to size



The P-touch 1000 from Brother.

An easy-to-use, hand-held labelling machine for the office or home that produces a wide variety of professional quality labels made to last. It's the P-touch 1000 electronic labeller from Brother.

Organising your world has never been easier

Whether you'd like to organise your workplace or simply sort things out around the home, it shouldn't be complicated. With the P-touch 1000 you just key in the word or number, choose the style, and then print. With Brother's professional quality TZ tapes you know these are labels that will last.

The P-touch 1000 is ideal for creating labels for any of the following:

Always at your side

- FILES AND FOLDERS
- CDS AND STATIONERY
- COMPUTER EQUIPMENT
- TOOLS AND GARDENING EQUIPMENT
- CLOTHING
- HOBBIES AND DIY

Printing that puts you in control

- Large printing area makes every label easier to read and printing on two lines means you can include as much detail as you'd like
- Choose from two different font styles **Oklahoma** **Helsinki**
- Choose up to ten different type styles plus framing and underlining
- Access over 50 symbols by pressing the symbol key **€ @ % © → ↵**

Long lasting labels that always look good

If you label something, you want the label to look good and to last. Brother's TZ labels are specifically designed to be hardwearing

P-touch labels are ideal for use both inside and outside in all weather conditions. They are able to withstand temperatures from -50°C to 300°C, this means the labels are resistant to freezing conditions and direct sunlight so they won't fade.

Available in a range of colours



As well as durable TZ tape, the range also includes the following tapes:

- Strong Adhesive Tape** - gives improved adhesion for those even more demanding applications and environments. In tests, this tape has shown improved performance on materials including: stainless steel, glass, PVC, acrylic, polypropylene and polyester-coated wood
- Iron-On Fabric Tape** - produces washable cloth labels that can be attached onto various fabrics by using an iron. This tape is ideal for labelling uniforms, work wear, bedding and table cloths



CDs



Laboratory



Valuables



Storage



VERTICAL
NORMAL
BOLD
ROMAN
ITALIC
ITALIC/OUTLINE
ITALIC/BOLD
ITALICSHADOW
OUTLINE
SHADOW
ITALIC

