

Search Results

Evaluate

- [FAQ's](#)
- [Press Releases](#)
- [Additional S...](#)

How to Buy

- [Bill of Material](#)
- [Favorite Products List](#)
- [Locate Distributor](#)

[Home](#) > [Product On-Line Catalog](#) > [Search Results](#) >

Current refinements (click to remove) Search Tips


[Panduit® Type F - Narrow Slot Wiring Duct \(Intrinsic Blue\)](#) > Text Search: 'F4X4IB6 '

Your search criteria matched only one product, shown below

Related Products

- [Panduit® Handheld](#)
- [Panduit® Notching](#)
- [Panduit® Nylon Riv](#)
- [Panduit® Divider We](#)
- [Panduit® Mounting](#)
- [More...](#)

F4X4IB6



Choose from 29 sizes of **PANDUIT**® Type F Wiring Duct from 0.5" x 0.5" up to 4.0" x 5.0". Used for general purpose control panel wiring in communication closets. Ideal for use with high-density terminal blocks. The non-slip cover conceals all wiring and is easy to install. The duct and cover form a flush sidewall providing increased capacity and improved aesthetics.

Specifications

- **Base and covers sold separately**
- Made of lead-free PVC
- UL Recognized continuous use temperature: 122°F (50°C)
- UL94 Flammability Rating of V-0
- Conforms with NFPA 79-2002 section 14.3.1

requirement for flame retardant material

- Available in Light Gray and White
- Provided with mounting holes

Features and Benefits

- Narrow finger/slot design allows further fanning of wires for neater wire management in high-density control panels
- **PANDUIT**® exclusive rounded edges protects hands and wiring/cablings from abrasion
- Non-slip cover stays in place during shipment, vibration and when in a vertical orientation, eliminating rework
- Flush cover design holds 10-12% more wires than traditional duct designs
- Double scoreline allows quick modification for larger cabling bundles saving installation time leading to a lower installed cost
- Specially formulated lead-free material eliminates health concerns associated with PVC that contains lead
- Double restricted slot design retains wire in slot for fast, easy wire installation or removal

Base and cover sold separately.

▪ Part Number	F4X4IB6
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Narrow slotted wiring duct. Base and covers sold separately.
▪ Product Type	Type F Narrow Slot Wiring Duct
▪ Material	Lead-Free PVC
▪ Color	Intrinsic Blue
▪ CSA Certified	Yes
▪ Height (In.)	4.10
▪ Height (mm)	104.1
▪ Length (ft.)	6
▪ Length (mm)	1828.8
▪ Width (In.)	4.25
▪ Width (mm)	108.0
▪ CE Compliant	Yes
▪ Duct Size W x H (In.)	4.25 x 4.10
▪ Duct Size W x H (mm)	108.0 x 104.1

Search Results

▪ Mounting Method	Standard Mounting Holes
▪ Pricing Description	Narrow Slot Flush Cover
▪ Slot Width (In.)	0.20
▪ Slot Width (mm)	5.0
▪ Cover Part Number	C4IB6
▪ Min. Order UOM	FT
▪ Min. Order Qty.	6
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.