

## MSC 10 fuse holder Phase + Neutral (1 mod.)

Fuse holder phase+neutral in a 17.5 mm - width compact module


**Compact Fuse Holder**



Nb. of Poles	Model without blown fuse indicator light		Model with blown fuse indicator light		Nb Mod	Pckg
	Cat. Number	Ref. number	Cat. Number	Ref. Number		
1+N	<b>MSC101N1M</b>	Y201317K	<b>MSC101N1MI</b>	C211050K	1	12
3+N	<b>MSC103N3M</b>	S218217D	<b>MSC103N3MI</b>	S226612D	3	4

Assembly accessories	Cat. Number	Ref. Number	Pckg
2-pole pin	<b>MSCMSDMAASS2</b>	G215125J	10*
3-pole pin	<b>MSCMSDMAASS3</b>	Q216145J	10*
4-pole pin	<b>MSCMSDMAASS4</b>	A217166J	10*

\* 10 Pins per bag




- Direct mounting on symmetrical DIN rail
- Indicator light (120/690V)\*
- Wiring cross sections:
  - single-pole: 1 x 16mm<sup>2</sup>
  - single-pole + neutral: 1 x 10 mm<sup>2</sup>
- Insulated to IP 20 standard
- Single-pole weight
  - 8x31 ; 63 g
  - 8x31 - Ph + N1M ; 63 g
  - 10x38 ; 63 g
  - 10x38 - Ph + N1M ; 68 g

\* With the indicator light a blown fuse can be quickly located if power is still on


## Modulostar CMS14



Size	CCD configurations	Cat. number w/o indicator light	Ref. number	Cat. number with indicator light	Ref. number	Pckg
14 x 51	1	<b>CMS141</b>	A331016F	<b>CMS141I</b>	L331049F	6
14 x 51	1+N	<b>CMS141N</b>	T331010C	<b>CMS141NI</b>	M331050C	3
14 x 51	2	<b>CMS142</b>	R331031C	<b>CMS142I</b>	M331004C	3
14 x 51	3	<b>CMS143</b>	J212091B	<b>CMS143I</b>	K331071B	2
14 x 51	3+N	<b>CMS143N</b>	D331042A	<b>CMS143NI</b>	Q331007A	1
14 x 51	4	<b>CMS144</b>	F331021A			1
14 x 51	N	<b>CMS14N</b>	T331056F			6
14 x 51 for fuses with striker	1			<b>CMS141AC</b>	F331044F	6
14 x 51 with microswitches (+ pre-isolation)	1	<b>CMS141M</b>	Z331038F	<b>CMS141MI</b>	S331055F	6
	2 (2 switches)	<b>CMS142M</b>	A331062C	<b>CMS142MI</b>	X331036C	3
	3	<b>CMS143M</b>	F331067B	<b>CMS143MI</b>	P331006B	2
(for fuses with striker)	3 (2 switches)	<b>CMS143M2</b>	H331069B	<b>CMS143M2I</b>	Y331037B	2
	3+N	<b>CMS143NM</b>	E331043A	<b>CMS143NMI</b>	Y331037A	1



## Accessories for CMS14



Description	Cat.number	Ref. number	Nb.Modules 17,5 mm	Pckg
Single-pole CMS14 auxiliary microswitch kit	<b>CMS14W1</b>	M218741	1.5	1
3-pole CMS14 auxiliary microswitch kit	<b>CMS14W2</b>	C219261	4.5	1
3-pole CMS14 2 auxiliary microswitch kit	<b>CMS14W3</b>	D219791	4.5	1
Auxiliary microswitch assembly pin (between 2 auxiliary microswitch kits)	<b>CMS1422PTH</b>	J214138		10
Enlargement pin for auxiliary microswitches	<b>CMS14BP</b>	F213629		10
Multi-pole assembly kit	<b>CMS1422PAK</b>	Z218223		10
Indicator light kit	<b>CMS14LIH</b>	A225653		1
Lock	<b>CMS14LOK</b>	M223525		1

## Modulostar CMS22



Size	CCD configurations	Cat. number w/o indicator light	Ref. number	Cat. number with indicator light	Ref. number	Pckg
22 x 58	1	<b>CMS221</b>	T331079F	<b>CMS221I</b>	B331086F	6
22 x 58	1+N	<b>CMS221N</b>	H331092C	<b>CMS221NI</b>	S215158C	3
22 x 58	2	<b>CMS222</b>	Q331122C	<b>CMS222I</b>	D331134C	3
22 x 58	3	<b>CMS223</b>	E331135B	<b>CMS223I</b>	D331134B	2
22 x 58	3+N	<b>CMS223N</b>	A331108A	<b>CMS223NI</b>	A218224A	1
22 x 58	4	<b>CMS224</b>	Q331099A			1
22 x 58	N	<b>CMS22N</b>	K331094F			6
22 x 58 for fuses with striker	1			<b>CMS22AC</b>	V331103F	6
22 x 58 with microswitches (+ pre-isolation) (for fuses with striker)	1	<b>CMS221M</b>	D219262F	<b>CMS221MI</b>	N331074F	6
	2 (2 switches)	<b>CMS222M</b>	E219792C	<b>CMS222MI</b>	P331098C	3
	3	<b>CMS223M</b>	Q222470B	<b>CMS223MI</b>	E331112B	2
	3 (2 switches)	<b>CMS223M2</b>	H222992B	<b>CMS223M2I</b>	E331112B	2
	3+N	<b>CMS223NM</b>	P200780A	<b>CMS223NMI</b>	W331104A	1



Fuse Holder

## Accessories CMS22

Description	Cat.number	Ref. number	Nb.Modules 17,5 mm	Pckg
Single-pole CMS22 auxiliary microswitch kit	<b>CMS22W1</b>	E211581	2	1
3-pole CMS22 auxiliary microswitch kit	<b>CMS22W2</b>	L212093	6	1
3-pole CMS22 2 auxiliary microswitch kit	<b>CMS22W3</b>	B212613	6	1
Auxiliary microswitch assembly pin (between 2 auxiliary microswitch kits)	<b>CMS1422PTH</b>	J214138		10
Enlargement pin for auxiliary microswitches	<b>CMS14BP</b>	F213629		10
Multi-pole assembly kit	<b>CMS1422PAK</b>	Z218223		10
Indicator light kit	<b>CMS14LIH</b>	A225653		1
Lock	<b>CMS14LOK</b>	M223525		1



## Drawings for CMS22

