

BT SERIES

SELF LOCKING COUPLING ADAPTOR


INTERFACE: H

TO FIT TYPICAL CONNECTOR: MIL-DTL-38999 SERIES III & IV

For modifications see page:



➤ Visit our on-line catalogue or contact sales on ➤ www.polamco.com ➤ sales@polamco.co.uk



DRAWING NOT TO SCALE
DIMENSIONS IN MM

IF THIS DOCUMENT IS PRINTED IT BECOMES UNCONTROLLED. CHECK THE LATEST ISSUE.

NCAGE CODE U5792



BT SERIES

SELF LOCKING COUPLING ADAPTOR

INTERFACE: H

TO FIT TYPICAL CONNECTOR: MIL-DTL-38999 SERIES III & IV

For modifications see page:



➤ Visit our on-line catalogue or contact sales on ➤ www.polamco.com ➤ sales@polamco.co.uk

EXAMPLE PART NUMBER	BT	H	1	- 17	- 08	- 1	- B	- SB	-AD
SERIES									
CONNECTOR INTERFACE									
ANGLE									
SHELL SIZE (TABLE 1)									
ENTRY SIZE (TABLE 2)									
MATERIAL (1-ALUMINIUM ALLOY)									
PLATING (TABLE 3)									
BAND REF									
ANTI-DECOUPLING									

SHELL SIZE	A THREAD	B MAX	T MIN	C MAX	D MAX	E MAX	F MAX	K +/- 0,5
09	M12 x 1.0	21,5	6,7	18,6	24,7	25,5	30,5	17,5
11	M15 x 1.0	24,6	10,2	19,2	25,9	26,5	32,2	17,5
13	M18 x 1.0	28,3	13,5	19,8	26,3	31,0	33,7	20,0
15	M22 x 1.0	32,4	16,2	20,2	27,2	37,0	35,2	24,5
17	M25 x 1.0	35,6	19,4	21,0	28,0	40,0	36,9	26,7
19	M28 x 1.0	38,5	21,8	21,3	28,3	44,5	38,5	27,0
21	M31 x 1.0	41,7	25,1	22,0	29,6	49,0	40,1	30,5
23	M34 x 1.0	43,9	28,2	22,7	29,5	51,5	41,6	31,5
25	M37 x 1.0	47,0	31,4	23,3	30,4	53,0	43,1	28,5

ENTRY SIZE	G MIN	H MAX
03	4,77	13,9
04	6,35	13,9
05	7,92	15,5
06	9,52	17,2
07	11,1	18,7
08	12,7	20,3
09	14,2	21,9
10	15,8	23,5
11	17,4	25,1
12	19,0	26,7
13	20,6	28,3
14	22,2	29,9
15	23,8	31,5
16	25,4	33,1
17	27,0	34,7
18	28,6	36,3
19	30,2	37,9
20	31,8	39,5
21	33,3	41,1
22	35,0	42,7
23	36,5	44,3
24	38,1	45,9

CODE	PLATING
B	CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
C	ELECTROLESS NICKEL
ZB	ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL

LIST NOT EXHAUSTIVE - FOR COMPREHENSIVE LIST AND SPECS SEE WEBSITE

DRAWING NOT TO SCALE
DIMENSIONS IN MM

IF THIS DOCUMENT IS PRINTED IT BECOMES UNCONTROLLED. CHECK THE LATEST ISSUE.

NCAGE CODE U5792

