



I.D. PRO® Plus, LS2000 & BradyMarker™ XC Plus Printer Labels - # WML-511-499

SIZE:	1.000" W x 0.750" H (25.400 mm W x 19.050 mm H)
MATERIAL:	Nylon Cloth
QTY/UOM:	250/Roll
CATALOG #:	WML-511-499
PRODUCT #:	32631

OVERVIEW SPECIFICATIONS

Description for I.D. PRO® Plus, LS2000 & BradyMarker™ XC Plus Printer Labels

Blank, printable, nylon cloth labels for the I.D. PRO® Plus, LS2000 & BradyMarker™ XC Plus printers. This material is a UL-recognized component when printed with R2000 and R5000 dot matrix ribbons. See UL file MH17154 for specific details.

Specification Of I.D. PRO® Plus, LS2000 & BradyMarker™ XC Plus Printer Labels

Application(s): Panel Identification, Through Hole - Top, Wire & Cable Marking

Agency Approval(s)/Compliance: Halogen-Free (DIN VDE 0472/parts 815), UL Recognized

Size: 1.000" W x 0.750" H (25.400 mm W x 19.050 mm H)

Printable Area: 1.000" W x 0.750" H (25.400 mm W x 19.050 mm H)

Max Characters Across: LARGE - I.D. PRO: 7, LS2000: 7. SMALL - I.D. PRO: 10, LS2000: 15

Max Lines of Print: I.D. PRO: 4, LS2000: 5

Label Type/Style: Label

Color: White

Finish: Matte

Qty Per Row: 1

Material Type: Nylon Cloth

Material Description: Nylon Cloth

Brady Material #: B-499

Safety Catalog: pg. 126

Recommended Ribbon Series: R5000, R2000

After Process: Yes, this material will work with this application

Printer Compatibility: BradyMarker XC Plus, I.D. PRO Plus, LS2000

Surface: Highly Textured, Low Surface Energy, Powder Coated, Smooth, Textured/Rough

Surface Mount Technology: No, this material does not work with this application

Through Hole Technology: Top: Yes. In extreme high temperatures, testing of this material is recommended, Bottom: No

Special Properties: High adhesion, Low profile

RoHS Compatibility: Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

QTY/UOM: 250/Roll