

Sets of HSS bi-metal hole saws in plastic cases

Type	Description	Article no.	Price / set €
EK 1	For electricians 6 HSS bi-metal hole saws Ø 22 - 29 - 35 - 44 - 51 - 64 mm + 2 arbor holders A2 and A4	106 305	
EK 2	For electricians 6 HSS bi-metal hole saws Ø 22 - 29 - 35 - 44 - 51 - 68 mm + 2 arbor holders A2 and A4	106 302	
Universal	10 HSS bi-metal hole saws Ø 19 - 22 - 25 - 29 - 35 - 38 - 44 - 51 - 57 - 64 mm + 2 arbor holders A2 and A4	106 303	
Super	10 HSS bi-metal hole saws Ø 22 - 25 - 32 - 35 - 41 - 44 - 51 - 54 - 60 - 64 mm + 2 arbor holders A2 and A4	106 304	
Premium	15 HSS bi-metal hole saws Ø 16 - 19 - 21 - 24 - 25 - 29 - 32 - 37 - 40 - 48 - 51 - 54 - 60 - 73 - 83 mm + 2 arbor holders A1 and A2 + 1 Pilot drill HSS Ø 6,35 mm x 82 mm + 1 Extension 300 mm, arbors for A1 and A2	106 318	



No. 106 304



No. 106 318

Sets of HSS Co 8 bi-metal hole saws in plastic cases

Type	Description	Article no.	Price / set €
PK 1	For plumbers 6 HSS Co 8 bi-metal hole saws Ø 19 - 22 - 29 - 38 - 44 - 57 mm + 2 arbor holders A2 and A4	126 301	
PK 2	For plumbers 9 HSS Co 8 bi-metal hole saws Ø 19 - 22 - 29 - 35 - 38 - 44 - 51 - 57 - 64 mm + 2 arbor holders A2 and A4	126 306	
EK 1	For electricians 6 HSS Co 8 bi-metal hole saws Ø 22 - 29 - 35 - 44 - 51 - 64 mm + 2 arbor holders A2 and A4	126 305	
EK 2	For electricians 6 HSS Co 8 bi-metal hole saws Ø 22 - 29 - 35 - 44 - 51 - 68 mm + 2 arbor holders A2 and A4	126 302	
Universal	10 HSS Co 8 bi-metal hole saws Ø 19 - 22 - 25 - 29 - 35 - 38 - 44 - 51 - 57 - 64 mm + 2 arbor holders A2 and A4	126 303	
Super	10 HSS Co 8 bi-metal hole saws Ø 22 - 25 - 32 - 35 - 41 - 44 - 51 - 54 - 60 - 64 mm + 2 arbor holders A2 and A4	126 304	
Premium	15 HSS Co 8 bi-metal hole saws Ø 16 - 19 - 21 - 24 - 25 - 29 - 32 - 37 - 40 - 48 - 51 - 54 - 60 - 73 - 83 mm + 2 arbor holders A1 and A2 + 1 Pilot drill HSS Ø 6,35 mm x 82 mm + 1 Extension 300 mm, arbors for A1 and A2	126 318	



No. 126 306



No. 126 304