



## Thermal Transfer Printable Labels - # THT-18-483-3

<b>SIZE:</b>	3.000" W x 1.000" H (76.200 mm W x 25.400 mm H)
<b>MATERIAL:</b>	Ultra Aggressive Polyester
<b>QTY/UOM:</b>	3,000/Roll
<b>CATALOG #:</b>	THT-18-483-3
<b>PRODUCT #:</b>	31332

### OVERVIEW **SPECIFICATIONS**

#### Description for Thermal Transfer Printable Labels

BradyBondz™ printable, ultra aggressive polyester labels for thermal transfer printers. Please Note: This material is UL & CSA approved with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to use.

#### Specification Of Thermal Transfer Printable Labels

**Application(s):** General & Industrial Identification, General ID, General Identification, Panel Identification, Voice/Data Identification

**Agency Approval(s)/Compliance:** CSA Approved, UL Recognized

**Size:** 3.000" W x 1.000" H (76.200 mm W x 25.400 mm H)

**Printable Area:** 3.000" W x 1.000" H (76.200 mm W x 25.400 mm H)

**Web Width:** 3.200" (81.28 mm)

**Label Type/Style:** Label

**Vertical Repeat:** 1.125" (28.58 mm)

**Color:** White

**Finish:** Gloss

**Qty Per Row:** 1

**Material Type:** Polyester

**Material Description:** Ultra Aggressive Polyester

**Brady Material #:** [B-483](#)

**General ID Catalog:** [pg. 92](#)

**Recommended Ribbon Series:** 6000

**Suggested Ribbon Part#:** R6002

**Acceptable Ribbon Series:** 6200, 4900, 4400 (colors)

**Printer Compatibility:** BBP81, Brady 1244, Brady 1344, Brady 200MVP Plus, Brady 2461, Brady 300MVP Plus, Brady 300X-Plus II, Brady 3481, Brady 360X-Plus II, Brady 600X-Plus II, Brady 6441, IP300, IP600, Tagus T200, Tagus T300, Thermal Transfer Printers

**Surface:** Highly Textured, Low Surface Energy, Powder Coated, Smooth, Textured/Rough

**Special Properties:** Designed for powder coated surfaces, Ultra-aggressive adhesive

**RoHS Compatibility:** Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

**QTY/UOM:** 3,000/Roll