



# Catamount™ Terminals

**NEW!**


**Catamount™ Terminals – Now in Convenient, Spillproof, Re-Usable Packaging!**


While poly bags keep their contents dry, they don't offer much other protection, and they aren't environmentally friendly. That's why Catamount™ terminals now come in sturdy plastic containers that safeguard the connectors inside against crushing and can be re-used or recycled when empty. T&B is always adding value to its products. With the introduction of a durable plastic container, the value of T&B's Catamount™ terminals has been significantly enhanced. No more lost or spilled terminals because of inadequate packaging.




**Vinyl Insulated Ring Terminals** 



Cat. No.	Wire Range	Bolt Size	Pkg Qty
TV18-6R-XV	22-16	#6	15
TV18-8R-XV		#8	
TV18-10R-XV		#10	
TV14-6R-XV	16-14	#6	15
TV14-8R-XV		#8	
TV14-10R-XV		#10	
TV10-8R-XV	12-10	#8	15
TV10-10R-XV		#10	
TV10-14R-XV		1/4"	





**Vinyl Insulated Fork Terminals** 

Cat. No.	Wire Range	Bolt Size	Pkg Qty
TV18-6F-XV	22-16	#6	15
TV18-8F-XV		#8	
TV14-6F-XV	16-14	#6	15
TV14-8F-XV		#8	
TV14-10F-XV		#10	
TV10-8F-XV	12-10	#8	15
TV10-10F-XV		#10	
TV10-14F-XV		1/4"	



**Vinyl Insulated Butt Splices**  

Cat. No.	Wire Range	Pkg Qty
TV18-BS-XV	22-18	15
TV14-BS-XV	16-14	15
TV10-BS-XV	12-10	15


**Vinyl Insulated Butt Splices Kit**  


Cat. No.	Wire Range	Qty	Pkg Qty
TV10-18-BS	22-18	5	15
	16-14	5	
	12-10	5	




**Nylon Insulated Wire Joints** 


Cat. No.	Wire Range	Pkg Qty
TN18-WJ-XV	22-16	15
TN14-WJ-XV	16-14	15
TN10-WJ-XV	12-10	15




**Vinyl Insulated Double Crimp Locking Fork** 


Cat. No.	Wire Range	Pkg Qty
TV18-10LFD-XV	22-16	15
TV18-6LFD-XV		
TV18-8LFD-XV		
TV14-10LFD-XV	16-14	15
TV14-6LFD-XV		
TV14-8LFD-XV		
TV10-10LFD-XV	12-10	15
TV10-6LFD-XV		
TV10-8LFD-XV		




**Vinyl Insulated Locking Fork Terminal** 


Cat. No.	Wire Range	Pkg Qty
TV18-10LF-XV	22-16	15
TV18-6LF-XV		
TV18-8LF-XV		
TV14-10LF-XV	16-14	15
TV14-6LF-XV		
TV14-8LF-XV		
TV10-10LF-XV	12-10	15
TV10-6LF-XV		
TV10-8LF-XV		




**Vinyl Insulated Female Disconnects – 250 Series** 


Cat. No.	Wire Range	Pkg Qty
TV18-250FD-XV	22-16	15
TV14-250FD-XV	16-14	15
TV10-250FD-XV	12-10	15




**Vinyl Insulated male Disconnects – 250 Series** 


Cat. No.	Wire Range	Pkg Qty
TV18-250MD-XV	22-16	15
TV14-250MD-XV	16-14	15
TV10-250MD-XV	12-10	15



**Non insulated Ring Terminals** 


Cat. No.	Wire Range	Pkg Qty
T14-10R-XV	16-14	15
T14-8R-XV		
T10-10R-XV	12-10	15
T10-14R-XV		
T10-8R-XV		




**Non insulated Fork Terminals** 

Cat. No.	Wire Range	Pkg Qty
T18-10F-XV	22-18	15
T18-8F-XV		
T14-10F-XV	16-14	15
T14-8F-XV		
T10-10F-XV	12-10	15
T10-14F-XV		
T10-8F-XV		



**Vinyl Insulated Blade Terminal** 


Cat. No.	Wire Range	Pkg Qty
TV18-10BL-XV	22-16	15
TV14-10BL-XV	16-14	15
TV14-18BL-XV	16-14	15
TV10-10BL-XV	12-10	15

**Vinyl Insulated Pin Terminal** 


Cat. No.	Wire Range	Pkg Qty
TV18-12PT-XV	22-16	15
TV14-12PT-XV	16-14	15
TV10-14PT-XV	12-10	15

**Vinyl Insulated Piggy Back Disconnect** 


Cat. No.	Wire Range	Pkg Qty
TV18-250PD-XV	22-16	15
TV14-250PD-XV	16-14	15
TV10-250PD-XV	12-10	15

**Vinyl Insulated Double Crimp Piggy Back Disconnect** 


Cat. No.	Wire Range	Pkg Qty
TV18-250PDD-XV	22-16	15
TV14-250PDD-XV	16-14	15
TV10-250PDD-XV	12-10	15

**Vinyl Fully Insulated Double Crimp Female Disconnect** 


Cat. No.	Wire Range	Pkg Qty
TVF18-250FDD-XV	22-16	15
TVF14-250FDD-XV	16-14	15
TVF10-250FDD-XV	12-10	15

**Vinyl Fully Insulated Female Disconnect** 


Cat. No.	Wire Range	Pkg Qty
TVF18-250FD-XV	22-16	15
TVF14-250FD-XV	16-14	15
TVF10-250FD-XV	12-10	15

**Vinyl Insulated Double Crimp Male Disconnect** 


Cat. No.	Wire Range	Pkg Qty
TV18-250FDD-XV	22-16	15
TV14-250FDD-XV	16-14	15
TV10-250FDD-XV	12-10	15

**Vinyl Insulated Double Crimp Male Disconnect** 


Cat. No.	Wire Range	Pkg Qty
TV18-250MDD-XV	22-16	15
TV14-250MDD-XV	16-14	15
TV10-250MDD-XV	12-10	15

**Nylon Fully Insulated Female Disconnect** 


Cat. No.	Wire Range	Pkg Qty
TNF18-250FD-XV	22-16	15
TNF14-250FD-XV	16-14	15
TNF10-250FD-XV	12-10	15

**Nylon Fully Insulated Male Disconnect** 


Cat. No.	Wire Range	Pkg Qty
TNF18-250MD-XV	22-16	15
TNF14-250MD-XV	16-14	15
TNF10-250MD-XV	12-10	15

**Nylon Fully Insulated Double Crimp Female Disconnect** 


Cat. No.	Wire Range	Pkg Qty
TNF18-250FDD-XV	22-16	15
TNF14-250FDD-XV	16-14	15
TNF10-250FDD-XV	12-10	15

**Nylon Fully Insulated Double Crimp Male Disconnect** 


Cat. No.	Wire Range	Pkg Qty
TNF18-250MDD-XV	22-16	15
TNF14-250MDD-XV	16-14	15
TNF10-250MDD-XV	12-10	15

**Vinyl Insulated Quick Splice** 

Cat. No.	Wire Range	Pkg Qty
TV18-00QS-V	22-18	5
TV14-00QS-V	18-14	5
TV10-00QS-V	12-10	5

**Nylon Fully Insulated Female Bullet** 

Cat. No.	Wire Range	Pkg Qty
TNF18-4FB-XV	22-16	15
TNF14-4FB-XV	16-14	15

**Nylon Fully Insulated Male Bullet** 

Cat. No.	Wire Range	Pkg Qty
TNF18-4MB-XV	22-16	15
TNF14-4MB-XV	16-14	15

**NOTE :** Disconnect tab size: .250" x .032"

Atlantic Region	Quebec Region	Ontario Region	Western Region	Thomas & Betts Limited
<b>Thomas &amp; Betts Limited</b> 106 Chain Lake Drive, Unit 2C Halifax, Nova Scotia B3S 1A8 Tel.: (902) 450-1307 Toll Free: 1-877-862-4357 Fax: (902) 450-1309	<b>Thomas &amp; Betts Limited</b> 7900 Taschereau Boulevard Building D, Suite 108 Brossard, Quebec J4X 1C2 Tel.: (450) 466-1102 Toll Free: 1-800-465-1399 Fax: (450) 466-1163	<b>Thomas &amp; Betts Limited</b> 2000 Argentia Road Plaza 5, Suite 500 Mississauga, Ontario L5N 2R7 Tel.: (905) 858-1010 Toll Free: 1-877-291-7771 Fax: (905) 858-1080	<b>Thomas &amp; Betts Limited</b> 6531-148th Street, #1 Surrey, British Columbia V3S 3C5 Tel.: (604) 598-9811 Toll Free: 1-866-540-8220 Fax: (604) 598-9840	<b>Thomas &amp; Betts Limited</b> 4836 Eleniak Road Edmonton, Alberta T6B 2S1 Tel.: (780) 424-7092 Toll Free: 1-888-664-5666 Fax: (780) 424-7093 Toll Free: 1-866-424-4082