



BMP21 Printer Kit with AC Adapter - # BMP21-KIT-110943

QTY/UOM:	1/Kit
CATALOG #:	BMP21-KIT-110943
PRODUCT #:	110943
LABEL SUPPLIES:	View Label/Ribbon Cartridges for the BMP21 Label Printer



[OVERVIEW](#) [FEATURES](#) [APPLICATIONS](#) [SPECIFICATIONS](#) [ACCESSORIES](#)

Description for BMP21 Printer Kit with AC Adapter

This BMP21 Printer Kit includes a BMP21 Portable Label Printer and a convenient AC adapter for powering your label maker without AA batteries. The BMP®21 Label Printer is a trademark of Brady Worldwide, Inc.

Features of the BMP®21 Label Printer

Prints on These Types of Label Constructions

- Self-Laminating Vinyl
- Permasleeve™ Wire Marker Sleeves
- Nylon Cloth
- Polyester
- Indoor/Outdoor Vinyl Film

More Types of Labels

- Banner Landscape/Portrait
- Wire
- Terminal Block
- Patch Panel
- Fixed Length

Easy-to-load cartridges - including the NEW self-laminating labels

Built in touch cell in labels and ribbon allows printer to automatically format label

6 font sizes - includes bold, auto sizing and bold auto sizing

80 different symbols - 13 specific to voice/data comm.

Barcoding – choose from 39 and 128

Automated serialization - includes multiple copies and increment options

Multiple print

Dual cutter buttons and label retention

Easy-to-read - 2" W x 1" H (50.8 mm W x 25.4 mm H) display with backlight

Built in bumper guards

Print and cut technology – press print once for multi-print or serial

Multi-function accessory with magnet, flashlight and wrist strap sold separately

Store, retrieve and delete label files

Automatic shut-off if not used in 10 minutes

Power source: 6 AA batteries – will print approximately 1,512 labels that are 2" (50.8 mm) long. AC power supply also available

12 month warranty

Applications of the BMP®21 Label Printer

- Wire and Applications of the BMPd cable marking
- Patch panels
- Control panel and component marking
- Workstation labels
- Maintenance and engineering
- Electrical data communications
- Field service and installation

5S/Visual Workplace
Storerooms and tool cribs
Construction
Laboratories
Asset and general ID
Work truck
General labeling
Any smooth, flat, curved, textured, or highly textured surfaces

Specification Of BMP21 Printer Kit with AC Adapter

Application(s): Barcode Labeling, Circuit Board Labeling, Data Communications Labeling, Facility, Safety & Maintenance Identification, General & Industrial Labeling, Healthcare Identification, Lean/5S Labeling, Panel Identification, Wire & Cable Marking

Label Supplies: [View Label/Ribbon Cartridges for the BMP21 Label Printer](#)

Text Sizes: 6 (6 to 40 point font)

Max Roll Length: 21'

Color Capability: Single Color Printing

Connectivity Options: None

Display: LCD

Keyboard: ABC

Materials Supported: Continuous/ 41 Stock parts

Memory: Last label

Multi-Line Print: Yes

PC Connectivity: No

Peripheral Printing: No

Power Supply: 6 AA's, AC Power (optional)

Print Resolution: 203 dpi

Print Rotation: No

Print Technology: Thermal Transfer

Printer Compatibility: BMP21

Continuous vs Die Cut Labels: Continuous labels only

Serialization: Yes

Stand Alone Printing: Yes

Warranty: 12 Months - See Terms and Conditions

Weight: 1.66 lbs

Includes: BMP21 Printer, M21-750-499 Label Cartridge, Quick Start Guide and AC Adapter

QTY/UOM: 1/Kit

Accessories for BMP21 Printer Kit with AC Adapter



Catalog #: [BMP21-AC](#)

BMP®21 AC Adapter - North America

AC Adapter for the BMP®21 Portable Label Printer.

1/Each

.

[View Product Details](#)



Catalog #: [BMP21-HC](#)

BMP®21 Hardside Carrying Case

1/Each

.

[View Product Details](#)



Catalog #: [BMP21-MAGNET](#)

BMP®21 Magnet Only Accessory

A magnet accessory for the BMP®21 Portable Label Printer.

1/Each

.

[View Product Details](#)



Catalog #: [BMP21-TOOL](#)

BMP®21 Multifunctional Accessory

A multifunctional accessory with flashlight for operating the BMP®21 printer with one hand.

1/Each

.

[View Product Details](#)