



**TLS 2200®/TLS PC Link™ BradyBondz™ Labels - #**  
PTL-35-423-PROP

<b>LEGEND:</b>	PROPERTY TAG
<b>SIZE:</b>	1.630" W x 0.750" H (41.400 mm W x 19.050 mm H)
<b>MATERIAL:</b>	Permanent Polyester
<b>QTY/UOM:</b>	250/Roll
<b>CATALOG #:</b>	PTL-35-423-PROP
<b>PRODUCT #:</b>	18438

OVERVIEW **SPECIFICATIONS**

**Description for TLS 2200®/TLS PC Link™ BradyBondz™ Labels**

BradyBondz™ Labels for the TLS 2200® & TLS-PC Link™ Thermal Transfer Portable Printers. Please Note: This material is UL, CSA & AGA approved with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to use.

**Specification Of TLS 2200®/TLS PC Link™ BradyBondz™ Labels**

**Application(s):** General & Industrial Identification, Through Hole - Top

**Agency Approval(s)/Compliance:** AGA Approved, CSA Approved, Halogen-Free (DIN VDE 0472/parts 815), UL Recognized

**Legend:** PROPERTY TAG

**Size:** 1.630" W x 0.750" H (41.400 mm W x 19.050 mm H)

**Printable Area:** 1.630" W x 0.750" H (41.400 mm W x 19.050 mm H)

**Label Type/Style:** Label

**Color:** Black on Silver

**Finish:** Gloss

**Qty Per Row:** 1

**Material Type:** Polyester

**Material Description:** Permanent Polyester

**Brady Material #:** B-423

**General ID Catalog:** [pg. 25](#)

**Recommended Ribbon Series:** R6010

**Suggested Ribbon Part#:** R6010

**Acceptable Ribbon Series:** R6210, R4410 (colors)

**After Process:** Yes, this material will work with this application

**Printer Compatibility:** BMP71, TLS 2200, TLS-PC Link

**Surface:** Smooth

**Surface Mount Technology:** No, this material does not work with this application

**Through Hole Technology:** Top: Yes. In extreme high temperatures, testing of this material is recommended, Bottom: No

**RoHS Compatibility:** Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

**QTY/UOM:** 250/Roll