

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [63811-4200](#)
Status: **Active**
Description: Hand Crimp Tool

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General


Product Family	Application Tooling
Series	T0102
Comments	Prototype and field repair
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Product Name	N/A
Survey	www.molex.com//review/apptool_survey.html
Tool Type	Handtool

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-6381142HM, TM-638000029, TM-638000029CN, TM-638000029DE, TM-638000029FR, TM-638000029IT, TM-638000029JP, TM-638000029KR, TM-638000029MY, TM-638000029PL, TM-638000029RU, TM-638000029SK, TM-638000029SP, TM-638000029TH, TM-638000029TW, TM-638000029VN



EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[T0102Series](#)

Use With

Loose piece terminals

Application Tooling | [FAQ](#)

Description	Product #
-------------	-----------

2.54mm Pitch	0334680003
--------------	------------

MX64™ Terminal, Tin (Sn) Plating, 18-20 AWG, Right Reel Payoff, Also used with MX123™ Female Receptacle Housing

2.54mm Pitch	0334670003
--------------	------------

MX64™ Terminal, Gold (Au) Plating, 22 AWG, Right Reel Payoff, Also used with MX123™ Female Receptacle Housing

2.54mm Pitch MX64™ Terminal, Gold (Au) Plating, 22 AWG, Left Reel Payoff, Also used with MX123™ Female Receptacle Housing	0334670004
2.54mm Pitch MX64™ Terminal, Gold (Au) Plating, 18-20 AWG, Right Reel Payoff, Also used with MX123™ Female Receptacle Housing	0334670005
2.54mm Pitch MX64™ Terminal, Gold (Au) Plating, 18-20 AWG, Left Reel Payoff, Also used with MX123™ Female Receptacle Housing	0334670006
2.54mm Pitch MX64™ Terminal, Tin (Sn) Plating, 22 AWG, Right Reel Payoff, Also used with MX123™ Female Receptacle Housing	0334680001
2.54mm Pitch MX64™ Terminal, Tin (Sn) Plating, 22 AWG, Left Reel Payoff, Also used with MX123™ Female Receptacle Housing	0334680002
2.54mm Pitch MX64™ Terminal, Tin (Sn) Plating, 18-20 AWG, Left Reel Payoff, Also used with MX123™ Female Receptacle Housing	0334680004

This document was generated on 04/13/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION