




Home > ... > Tools > Cordless Tools > M18™ Cordless LITHIUM-ION System > M18 FUEL™ 1/2" Drill/Driver Kit

M18 FUEL™ 1/2" Drill/Driver Kit 2603-22



5.0 [Read 5 Reviews](#) [Write a Review](#)

Milwaukee M18 FUEL™...A New Breed of Cordless Tool. Utilizing the Most Advanced Technologies in the World, FUEL™ Delivers Unrivalled Performance in a Compact Structure. Built for the Most Demanding Professionals in the World.

With up to 725 in lbs of torque, the M18 FUEL™ Drill Driver is the most powerful drill in its class. The new Milwaukee designed and built POWERSTATE™ Brushless Motor provides unmatched power and sustained torque to complete the toughest of applications. The POWERSTATE™ Brushless Motor outperforms all leading competitors and delivers up to 10X longer motor life for maximum durability. Powered by the most durable battery pack on the market – REDLITHIUM™, the M18 FUEL™ Drill Driver delivers up to 50% more run-time than the competition. The M18™ REDLITHIUM™ batteries provide longer battery life, with over 5X more recharges than leading competitors. A battery fuel gauge displays remaining charge for less down time on the job. The M18 FUEL™ Drill Driver contains the most advanced electronic system on the market, with REDLINK PLUS™ intelligence. REDLINK PLUS™ electronics provide total system communication with overload protection. The M18 FUEL™ Drill Driver comes with the new multi-voltage charger, so you can charge all M12™ and M18™ batteries with one charger. A new contoured soft grip gives

Includes

- 2603 M18™ FUEL 1/2" Drill/Driver
- (2) M18™ HIGH CAPACITY REDLITHIUM™ Battery Packs
- Multi-Voltage Charger

FEATURES

- POWERSTATE™ Brushless Motor: Delivers up to 725 in lbs of torque with maximum sustained torque to complete the toughest of applications
- REDLITHIUM™ Battery Technology: Superior pack construction, electronics, and performance deliver more work per charge and more work over pack life than any battery on the market
- REDLINK PLUS™ Intelligence: The most advanced system of cordless power tool electronics. Provides optimized performance and overload protection using total system communication between tool, battery and charger.

SPECIFICATIONS

Volts	18V
Torque	725 in-lbs
Speed	2 Speed
RPM	0-550 / 0-1,850 RPM
Chuck Type	1/2" Metal Single Sleeve - Ratcheting Lock
Metal Sleeve	Yes
Ratcheting Lock	Yes
On Board Fuel Gauge	Fuel Gauge on Battery
LED Light	Yes
Battery	REDLITHIUM™
Batteries Included	(2) M18™ HIGH CAPACITY REDLITHIUM™ Battery Packs
Charger	NEW M18™ and M12™ Multi-Voltage Charger
Charge Time	1 Hour
Tool Length	7.9 in
Tool Weight (w/battery)	4.9 lbs