


[Home](#) > ... > [Shockwave Impact Duty™ Driver Bits](#) > 35pc Shockwave™ Drilling & Driving Bit Set

35pc Shockwave™ Drilling & Driving Bit Set 48-32-4402



3.8 [Read 4 Reviews](#) [Write a Review](#)

Milwaukee® Shockwave Impact Duty™ Drill Bits and Driver Bits are engineered for extreme durability and up to 10x life. Made from proprietary steel and heat treated to control hardness, the Shockwave Impact Duty™ Driver Bits feature an innovatively designed geometric shock absorption zone to extend life. The forged tip allows for a secure grip and maximum contact eliminating stripping or slipping. The Shockwave™ Impact Duty Hex Drive Drill Bits feature the Milwaukee Thunderbolt® web for durability and chip removal paired with taper-fit construction for a stronger bit with less wobble. The drill bits include a 135° split point to allow the bit to start on contact and eliminates walking. Broadly targeting cordless users, the Shockwave™ Impact Duty accessory line is not only ideal for heavy duty impact applications, but delivers a full system solution for all the user's drilling and fastening needs. **Broadly targeting cordless users, the Shockwave™ Impact Duty accessory line** is not only ideal for heavy duty impact applications, but delivers a full system solution for all the user's drilling

Includes

ECX™: 1" - (1) ECX1, (1) ECX2
Phillips Bits: 1" - (1) Ps, (2) P2, (1) P3
Phillips Power Bits: 2" - (1) P1, (1) P2
Phillips Power Bits: 3-1/2" - (1) P2
Square Bits: 1" - (1) SQ1, (2) SQ2, (1) SQ3
Square Power Bits 2" - (1) SQ1, (1) SQ2, (1) SQ3
Square Power Bits: 3-1/2" - (1) SQ2
Torx Power Bits: 2" (1) T15, (1) T20, (1) T25, (1) T30
Slotted Power Bits: 2" (1) SL1/8", (1) SL3/16", (1) SL1/4"
Magnetic Nut Drivers: (1) 1/4" Red, (1) 5/16" Amber, (1) 3/8" Blue
1/4" Hex Shank Drill Bits: (1) 1/8", (1) 5/32"(1) 3/16", (1) 7/32", (1) 1/4"
(1) Magnetic Bit Holder
Socket Adapters: (1) 1/4" hex shank to 3/8" Square
(1) 1/4" hex shank to 1/2" Square

FEATURES

- Geometric design provides the shock absorption
- Proprietary steel and heat treat process for maximum strength and durability
- Forged tips for maximum grip.

SPECIFICATIONS

Diameter	1/4 in
Length	1 in and 2 in
Package Quantity	35 pieces

RELATED ARTICLES

[Milwaukee Shockwave Impact Duty Accessories Review](#)

[Milwaukee® Introduces New Shockwave Impact Duty™ Accessories](#)