

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

08-70-0102

Status:


Active

Overview:

SPOX™ BMI

Description:

2.50mm Pitch SPOX™ Wire-to-Wire Male Crimp Terminal, Reel



Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [Product Specification PS-5102-003 \(PDF\)](#)
- [Product Specification PS-5102-005 \(PDF\)](#)
- [Product Specification PS-5102-006 \(PDF\)](#)
- [Product Specification PS-51191-003 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family

Series

Application

Crimp Quality Equipment

Overview

Product Name

Crimp Terminals

5241

Signal

Yes

SPOX™ BMI

SPOX™

Physical

Gender

Material - Metal

Material - Plating Mating

Material - Plating Termination

Packaging Type

Plating min - Mating

Plating min - Termination

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

Male

Brass

Tin

Tin

Reel

0.889µm

0.889µm

Crimp or Compression

1.15-1.90mm

22, 24, 26, 28

N/A

Material Info

Old Part Number

UPC

5241T

800753640511

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-5102-003, PS-5102-005, PS-5102-006,
PS-51191-003
SD-5241*

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

5241Series

Mates With

50802 female crimp terminal

Use With

5240

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	0638190800
FineAdjust™	0639004600
Applicator for Wire-to-Board and Wire-to-Wire Terminal, 22-28 AWG Wire	
T2 Terminator	0639104600
Tooling Die	

Japan

Description	Product #
Applicator for M211A	<u>0011260050</u>
Bench Press, 22-28	
AWG Wire	
Hand Extraction Tool	<u>0011260060</u>

This document was generated on 06/19/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION