

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

53015-0210

Status:

Active

Overview:

MicroBlade™

Description:

2.00mm Pitch MicroBlade™ Wire-to-Board Header, Right Angle, 2 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-51004-002 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

53015

Application

Signal, Wire-to-Board

Overview

MicroBlade™

Product Name

MicroBlade™

Physical

Breakaway

No

Circuits (Loaded)

2

Durability (mating cycles max)

30

First Mate / Last Break

No

Flammability

94V-0

Glow-Wire Compliant

No

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

Yes

Material - Metal

Phosphor Bronze

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Nylon

Number of Rows

1

Orientation

Right Angle

PC Tail Length

3.50mm

PCB Locator

No

PCB Retention

Yes

PCB Thickness - Recommended

1.60mm

Packaging Type

Bag

Pitch - Mating Interface

2.00mm

Polarized to PCB

No

Shrouded

Fully

Stackable

No

Surface Mount Compatible (SMC)

No

Temperature Range - Operating

-20°C to +85°C

Termination Interface: Style

Through Hole

Electrical

Current - Maximum per Contact


2A

Voltage - Maximum

125V

Material Info

Reference - Drawing Numbers



EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

53015Series

Mates With

51004 Crimp Housing, 50011 Crimp Terminal

Product Specification	PS-51004-002, RPS-51004-001, RPS-51004-002, RPS-51004-003, RPS-51004-008, RPS-51004-010, RPS-51004-011, RPS-51004-014, RPS-51004-015, RPS-51004-016, RPS-51004-017, RPS-51004-018, RPS-51004-019, RPS-51004-020, RPS-51004-021, RPS-51004-022, RPS-51004-023, RPS-51004-024, RPS-51004-025, RPS-53014-001
Sales Drawing	SD-53015-**10

This document was generated on 05/01/2012
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION