

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [63900-4500](#)  
**Status:** **Active**  
**Description:** FineAdjust™ Applicator for insulation OD 1.30-1.85mm - 20-24 AWG

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**


Product Family	Application Tooling
Series	T2501
Comments	See Tooling Specification (PDF) Above, Terminals will accommodate the UL1007 wires
Function	Crimp
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Product Name	FineAdjust™
Survey	<a href="http://www.molex.com//review/apptool_survey.html">www.molex.com//review/apptool_survey.html</a>
Tool Type	Applicator

**Material Info**

**Reference - Drawing Numbers**

Application Tooling Documents

ATS-639004500, TM-638000029, TM-638000029CN, TM-638000029DE, TM-638000029FR, TM-638000029IT, TM-638000029JP, TM-638000029KR, TM-638000029MY, TM-638000029PL, TM-638000029RU, TM-638000029SK, TM-638000029SP, TM-638000029TH, TM-638000029TW, TM-638000029VN, TM-638004900, TM-638004900CN, TM-638004900SP



**EU RoHS**  
**ELV and RoHS**  
**Compliant**  
**REACH SVHC**  
 Not Reviewed  
**Low-Halogen Status**  
**Not Reviewed**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**  
 T2501Series

**Use With**  
 Molex TM-3000™, 0638017200 , 0638017300 , Molex TM-2000™, 0638008300 , 0638008400 , most industry standard presses, or wire process machines

Application Tooling Description	FAQ Product #
Micro-Fit 3.0™ Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 20-24 AWG, Reel	0430300001
Micro-Fit 3.0™ Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 20-24 AWG, Reel	0430300002
Micro-Fit 3.0™ Crimp Terminal, Female,	0430300003

with Select Gold (Au)  
Plated Phosphor  
Bronze Contact,  
20-24 AWG, Reel  
Micro-Fit 3.0™ Crimp0430310001  
Terminal, Male,  
with Tin (Sn) Plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Reel  
Micro-Fit 3.0™ Crimp0430310002  
Terminal, Male, with  
Gold (Au) Plated Tin/  
Brass Alloy Contact,  
20-24 AWG, Reel  
Micro-Fit 3.0™ Crimp0430310003  
Terminal, Male, with  
Select Gold (Au)  
Plated Tin/Brass  
Alloy Contact, 20-24  
AWG, Reel

This document was generated on 04/27/2012

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**