


Triplett Case Styles & Construction

G SERIES




120-G 220-G 320-G 420-G 520-G



CASE & COMPOSITION:
Thermoplastic front and back,
four stud mounting.

OPTIONS AVAILABLE:
Half-Bezel for behind panel
mounting, Illumination Kit and
Shallow Barrel (page 19)

GL SERIES



220-GL 320-GL 420-GL 520-GL 820-GL



CASE & COMPOSITION:
Glass window, flat black thermo-
setting plastic case, two stud
mounting except 220-GL and 820-
GL have four stud mounting only.
820-GL contains contoured base
with sealed meter movement per-
mitting utilization of lower part of
front for mounting controls,
switches, etc.

OPTIONS AVAILABLE: Three and four stud mount-
ing for 320-GL, four stud mounting for 420-GL & 520-GL.

GL/B SERIES



320-GL/B 420-GL/B 520-GL/B



CASE & COMPOSITION:
Glass window, flat black thermo-
setting plastic case. Integral bezel
provides behind the panel mount-
ing. Requires minimum panel space
for better utilization of panel area.

R SERIES



420-R

CASE & COMPOSITION:
Thermoplastic front and thermosetting
plastic back with flat scale arc.

PHENOLIC SERIES

CASE & COMPOSITION: Glass window, thermosetting
plastic case, four stud mounting for Models 227-T, 327-T, 420 &
626, three stud mounting for Models 221-T & 321-T.

OPTIONS AVAILABLE: Illumination Kits available for certain
models- Please Contact Factory.



227-T



327-T




221-T



321-T




420



626

EDGEWISE SERIES



.5-E 120 220-E 320-E 420-E

320-ED
320-EG



CASE & COMPOSITION:

All case housing materials selected for their excellent electrical char-
acteristics and strengths. The .5-E has a thermoplastic front and steel
back. All models have thermoplastic windows except Models 320-ED
& 320-EG which have sealed glass windows. Model 320-EG* is
constructed to withstand rough environmental and industrial applica-
tions. Standard meter; horizontal mounting, barrel down, zero left
(except zero center models)

OPTIONS AVAILABLE: Bezels available for Models 220-E,
320-E, 420-E. Models 320-E, 320-EG and 420-E can be mounted from
front or rear of panel. Also available for vertical mounting, barrel right,
zero bottom.
* Includes steel mounting brackets.

RUGGEDIZED SERIES



127-HR



221-HR



321-HR

CASE & COMPOSITION:
Thermoplastic front, steel back.

**THE FAMOUS TRIPLETT BAR-RING®
SELF-SHIELDED CONSTRUCTION**

Not affected by magnetic panels or substantially by stray magnetic fields.