

# USB2.0 4 Port Hi-Speed Hub


pro-SIGNAL



## Features:

- USB V2.0 Specifications compatibility
- High-speed of 480 Mbps data transfer rate (Vs. 12 Mbps of USB 1.1 and 400 Mbps of IEEE 1394 firewires)
- Plug and play capability with USB devices
- Supports Self-Powered Mode, using Switching power indicated by power LED
- Hot-Swappable
- Connects up to a maximum of 127 USB devices through cascading multiple hubs
- Over current detection and protection with LED status indicators
- 4 external auto speed selectable USB Type A downstream ports, supporting 1.5, 12, and 480 Mbps

## MAC OS X(10)



## Introduction :

The USB 2.0 High-Speed Hub has 4 ports that will connect to either the USB Revision 2.0 High-Speed or the USB Revision 1.1 peripheral device. This high-speed hub allows you to add multiple high-performance USB 2.0 peripherals to the PC. Moreover, this product is fully backward compatible with the USB Revision 1.1 products, meaning your previously invested USB 1.1 devices can continue to function as usual. The USB 2.0 High-Speed Hub is fully compliant with the USB 2.0 specifications and permits you to connect up to a maximum of 127 USB devices to your PC through daisy-chain. Furthermore, with its increased bandwidth of 480 Mbps (exceeding that of IEEE 1394 firewires with 400 Mbps), this hub will allow you to connect devices that consume a great deal of bandwidth such as external storage devices, scanners, printers, DVD drives, CD-RW drives, MO (Magneto-Optical) drives, and digital cameras / camcorders to your computer

## System Requirements

IBM Compatible Pentium-233 MHz or faster and MAC PCs  
64Mb RAM or more  
PC or MAC with available USB ports  
Systems with OS: MS Windows 98SE / ME / 2000 / XP

## Part Number Table

| Description            | Part Number |
|------------------------|-------------|
| USB HUB, 2.0, External | CS07986     |

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of the Group. © Premier Farnell plc 2012.

[www.element14.com](http://www.element14.com)  
[www.farnell.com](http://www.farnell.com)  
[www.newark.com](http://www.newark.com)  
[www.cpc.co.uk](http://www.cpc.co.uk)

pro-SIGNAL