


PRODUCT SPECIFICATION































Brand	C.K
Product Range	Switch key
Catalogue number	4451
Date	20/02/2007

Range Description
Universal Switch Key

- Features**
- A multipurpose tool designed for use on locking systems of: gas, electric, and water cupboards in industry and/or technical equipment in buildings such as air conditioning, stop valves, mains consoles etc
 - Unique adapter to convert to an emergency screwdriver



Item Number	Item Description	EAN No	Commodity code	Carton Qty
495002	Universal switch key	5051074950024	82041100	10
495015	Universal switch key	5051074950154	82041100	1

<p>Technical product information</p>	<p>Body – Die cast Aluminium Double ended screwdriver bit: PH1 x slotted 1.0x7mm</p> <p>Adaptors:</p> <table border="0"> <thead> <tr> <th></th> <th></th> <th>495002</th> <th>495015</th> </tr> </thead> <tbody> <tr> <td>Outside diameter 14mm Square A/F 8mm</td> <td></td> <td></td> <td></td> </tr> <tr> <td>Outside diameter 12mm Square A/F 6mm</td> <td></td> <td></td> <td></td> </tr> <tr> <td>Outside diameter 12mm Square A/F 7mm</td> <td></td> <td></td> <td></td> </tr> <tr> <td>Outside diameter 9mm Square A/F 5mm</td> <td></td> <td></td> <td></td> </tr> <tr> <td>Outside diameter 14mm Triangle A/F 9mm</td> <td></td> <td></td> <td></td> </tr> <tr> <td>Across lugs 14mm Bore 5mm</td> <td></td> <td></td> <td></td> </tr> <tr> <td>A/F Major 10mm A/F Minor 4mm</td> <td></td> <td></td> <td></td> </tr> </tbody> </table> <p>A/F = Across Flats</p>			495002	495015	Outside diameter 14mm Square A/F 8mm				Outside diameter 12mm Square A/F 6mm				Outside diameter 12mm Square A/F 7mm				Outside diameter 9mm Square A/F 5mm				Outside diameter 14mm Triangle A/F 9mm				Across lugs 14mm Bore 5mm				A/F Major 10mm A/F Minor 4mm			
		495002	495015																														
Outside diameter 14mm Square A/F 8mm																																	
Outside diameter 12mm Square A/F 6mm																																	
Outside diameter 12mm Square A/F 7mm																																	
Outside diameter 9mm Square A/F 5mm																																	
Outside diameter 14mm Triangle A/F 9mm																																	
Across lugs 14mm Bore 5mm																																	
A/F Major 10mm A/F Minor 4mm																																	
Standards compliance	None applicable																																
User health and safety information	None applicable																																
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations																																
Material safety data	None applicable																																
Warranty	C.K switch keys are guaranteed for life against imperfect materials or workmanship																																
Country of origin	Germany																																

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
495002	70	14	70	77	85	15	163	84
495015	70	14	70	77	85	15	163	84

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
495002	165	220	80	917		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
495002	15	Blister	1	Backing card			77	Box
495015	15	Blister	1	Backing card				