

## HDC enclosures HDC 24B ALU

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

### General ordering data

Order No.	<a href="#">1213900000</a>
Type	HDC 24B ALU
Version	HDC enclosures, Size: 8, Protection degree: IP 65, Bulkhead enclosure, End-locking clamp, lower side, Standard
GTIN (EAN)	4008190176303
Qty.	1 pc(s).

**HDC enclosures  
HDC 24B ALU**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Length	143 mm	Width	74.4 mm
Height	29.3 mm	Mounting dimension - width	130 mm
Mounting dimension - height	32 mm	Net weight	177 g

**Dimensions**

Total length housing	120 mm	Width housing C	43 mm
Width base C1	47 mm	Height of housing B	29.3 mm
Height of base B1	5.3 mm	Hole pitch length A2	130 mm

**General data**

Housing main material      diecast aluminium

**Version**

Design of housing	Bulkhead enclosure	Size	8
Design	Standard	Top part/bottom part/lid	lower part
Design of locking system	End-locking clamp, lower side		

**Classifications**

ETIM 2.0	EC000437	ETIM 3.0	EC000437
UNSPSC	30-21-18-01	eClass 4.1	27-14-08-05
eClass 5.1	27-14-34-19	eClass 6.0	27-26-12-03
eClass 7.0	27-44-02-02		

**Approvals**

Approvals



**Downloads**

PDF	<a href="#">1213900000_HDC_24B_ALU_STP_Blatt_1.pdf</a>
IGES	<a href="#">1213900000_HDC_24B_ALU_STP.igs</a>
VRML	<a href="#">1213900000_HDC_24B_ALU_STP.wrl</a>
EPLAN	<a href="#">1213900000.MZF</a>
3-D model	