



## General Information

<b>Kit Part Number:</b>	<a href="#">2110856-5</a>
<b>Description:</b>	Panel Mount Double-Row Dual-Barrier Strip with Wire Clamping Screws and Hardware Kit
<b>Application:</b>	HVAC Systems, Industrial Controls, Power Supplies, Telecommunications, Test Equipment, Traffic Signals
<b>Family:</b>	Double-Row Dual-Barrier Strip
<b>TE Brand:</b>	BUCHANAN Products
<b>Solution:</b>	Field Wiring
<b>Product Type:</b>	Double-Row Dual-Barrier
<b>Number of Pieces:</b>	14
<b>RoHS:</b>	Yes

## Specifications

<b>Circuit Size(s):</b>	2, 3, 4, 5, 6, 8, 10
<b>Current Rating:</b>	20A
<b>Mounting Style:</b>	Panel Mount
<b>Pitch:</b>	0.437"
<b>Rows:</b>	Double Row
<b>Terminal Type:</b>	Wire Clamping Screws
<b>Tool Included:</b>	No
<b>Voltage Rating:</b>	300V
<b>Wire Gauge (AWG):</b>	22-14

## Product Highlights

Double-Row Dual-Barrier Strips for wire-to-wire applications allow end users to complete the wiring to a separate screw without disturbing the factory wiring. They also have increased current carrying capability.

### Features and Benefits

- Closed bottom design allows for mounting direct to sheet metal panel
- Molding to length
- Accessories such as Quick Connect Tabs and Jumpers are available

### Applications

- Industrial Controls
- Test Equipment
- HVAC
- Power Supplies
- Traffic Signals
- Telecom




**Bill of Materials**

Part No.	Qty In Kit	Description	Datasheet	P/N Details	Search Distributors Inventory
<a href="#">1546671-2</a>	2	0.437" Pitch, 2 Circuit Double-Row Dual-Barrier Strip, 22-14...	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">1546671-3</a>	2	0.437" Pitch, 3 Circuit Double-Row Dual-Barrier Strip, 22-14...	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">1546671-4</a>	2	0.437" Pitch, 4 Circuit Double-Row Dual-Barrier Strip, 22-14...	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">1546671-5</a>	2	0.437" Pitch, 5 Circuit Double-Row Dual-Barrier Strip, 22-14...	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">1546671-6</a>	2	0.437" Pitch, 6 Circuit Double-Row Dual-Barrier Strip, 22-14...	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">1546671-8</a>	2	0.437" Pitch, 8 Circuit Double-Row Dual-Barrier Strip, 22-14...	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">1-1546671-0</a>	2	0.437" Pitch, 10 Circuit Double-Row Dual-Barrier Strip, 22-1...	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>

**Recommended Tool**

**Part No.**

**Included in Kit**





Kit Part No. **2110856-5**

**TE** Authorized Distributor | Double-Row Dual-Barrier Category

### BILL OF MATERIALS


To re-order this kit, please visit [www.proteckits.com/Kit/2110856-5](http://www.proteckits.com/Kit/2110856-5)

TE Part No.	Qty	Bin Location	Description
3294622-6	2	1	5.837" Pitch, 24 Contact Double-Row Dual-Barrier (DRA) 23-24 AWG, 19 Lines, 100-100, with 19mm Clearance Spacers
3294622-6	2	2	5.837" Pitch, 4-Channel Double-Row Dual-Barrier (DRB) 23-24 AWG, 19 Lines, 100-100, with 19mm Clearance Spacers
3294622-6	2	3	5.837" Pitch, 4-Channel Double-Row Dual-Barrier (DRB) 23-24 AWG, 19 Lines, 100-100, with 19mm Clearance Spacers
3294622-6	2	4	5.837" Pitch, 4-Channel Double-Row Dual-Barrier (DRB) 23-24 AWG, 19 Lines, 100-100, with 19mm Clearance Spacers
3294622-6	2	5	5.837" Pitch, 4-Channel Double-Row Dual-Barrier (DRB) 23-24 AWG, 19 Lines, 100-100, with 19mm Clearance Spacers
3294622-6	2	6	5.837" Pitch, 4-Channel Double-Row Dual-Barrier (DRB) 23-24 AWG, 19 Lines, 100-100, with 19mm Clearance Spacers
3294622-6	2	7	5.837" Pitch, 4-Channel Double-Row Dual-Barrier (DRB) 23-24 AWG, 19 Lines, 100-100, with 19mm Clearance Spacers
3294622-6	2	8	5.837" Pitch, 4-Channel Double-Row Dual-Barrier (DRB) 23-24 AWG, 19 Lines, 100-100, with 19mm Clearance Spacers

Bin Diagram  
This edge to Align

Additional kits available at [www.proteckits.com](http://www.proteckits.com) or contact a TE-Connectivity authorized distributor

Assembled by Waldom Electronics in the USA





**Double-Row Dual-Barrier Category**

 **TE** Authorized  
connectivity Distributor

Kit Part No. **2110856-5**

**BUCHANAN  
Terminal Block Kit**

Panel Mount Double-Row Dual-Barrier Strip  
with Wire Clamping Screw and Hardware

- 0.437" Pitch
- 2, 3, 4, 5, 6, 8 and 10 Circuits
- 22-14 AWG
- 20 Amps, 500 Volts

Additional Kits available at [www.productkits.com](http://www.productkits.com)

BUCHANAN, TE Connectivity, TE connectivity logo and TE logo are trademarks of the TE Connectivity Ltd. family of companies.

**WARNING:** Failure to follow all instructions, including using only approved TE tooling (if applicable), can result in improper install failure and/or crimping which is dangerous and may cause or contribute to electrical fire. Should be used only by individuals with proper training and experience.

**14**  
pieces



0 10151 26921 1

Product from TE Connectivity.  
Kits designed and assembled  
by Waldom Electronics.