



Unfluxed Desoldering Braid

1830-1833

Desoldering braid (wick) is pre-fluxed copper braid that is used to remove solder, which allows components to be replaced and excess solder to be removed.

Techspray wick is available in static dissipative bobbins (except where indicated) for static sensitive environments.



Use your own flux -- ideal for aqueous process

For customers who use water-soluble flux, or their own flux for aqueous processes.



Size chart:

Braid #	Color Code	Width (in)	Width (mm)
#1	White	0.035	0.9
#2	Yellow	0.055	1.4
#3	Green	0.075	1.9
#4	Blue	0.098	2.5

- Apply your own flux
- Ideal for aqueous fluxes
- Allows flux matching in process
- Exceeds MIL-F-14256, Type
- Anti-static spool (except where indicated)

Product Packaging

1830-10F
Unfluxed White #1 Braid - AS
10'
25 units/case



1831-10F
Unfluxed Yellow #2 Braid - AS
10'
25 units/case



1832-5F
Unfluxed Green #3 Braid - AS
5'
25 units/case



1833-10F
Unfluxed Blue #4 Braid - AS
10'
25 units/case





Chemical & Physical Properties

Appearance	
Odor	
Flash Point	
VOC (EPA)	
VOC (CARB)	
Boiling Point	
Density	

Chemical Composition

CHEMICAL NAME	CAS #
Copper	7440-50-8

Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America

Techspray
 P.O. Box 949
 Amarillo, TX 79105
 800-858-4043
 email: tsales@techspray.com

Europe

ITW Contamination Control BV
 Saffierlaan 5
 2132 VZ Hoofddorp
 The Netherlands
 +31 88 1307 400
 email: info@itw-cc.com

Countries Outside US

Call to locate a distributor in your country

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

